






N ATTENUATOR 10 DB 3 GHZ 50W

PAGE 1/2 ISSUE 22-03-16B SERIES PART NUMBER R417010130

SCALE 1:2







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
5 1	074111 F00 07FF1	DAGGNATED	
Body	STAINLESS STEEL	PASSIVATED	
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Outer contact	-	-	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINA		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK PAINTING	





N ATTENUATOR 10 DB 3 GHZ 50W

PAGE 2/2	ISSUE 22-03-16B	SERIES ATTENUATOR	PART NUMBER R417010130
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2	2 - 3
V.S.W.R (≤)	1.10	1.25	1.35
Deviation(±dB)	0.70	0.70	0.70

Operating Frequency Range	DC - 3	GHz
Impedance	50	Ω
Nominal Attenuation	10	dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C		W (Free Air Cooled)
	50	W (Conduction Cooled)
For conduction cooling, a plate 500 cm2 x 3 mm(78 sq.in*1/8) min. is required		


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	290,3900 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS