




PCB Layout(Pattern side)



Circuit Diagram

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
寿命试验 Operating Life	100,000 cycles 70,000 cycles

SHRAPNEL	
CODE	MATERIAL/QTY
D2	SUS/1PCS
D4	SUS/2PCS

TOTAL HEIGHT	
CODE	G
A1	2.0
A2	2.5

OPERATING FORCE	
CODE	VIGOR
B2	180±30gf
B3	250±30gf

Ⓕ	Dust film	1	Polyimide tape		
Ⓔ	Terminal	4	Phosphorus bronze	Silvering	
Ⓓ	Reed	2	SUS	Silver covered	
Ⓒ	Button	1	Silica gel	Blue	
Ⓑ	Cover	1	SUS	Natural	
Ⓐ	Base	1	LCP	Black	
NO.	Name	Number	Qty	Materil	Remarks

Dongguan Usakro Electronic Technology Co., Ltd.

design	date	name	UK-B0288-SP25Y
Review	date	name	3*4
Approved	date	name	
Drawing number:			
modify	Review	Approved	Tolerance not specified
Proportion	1:1	unit	mm
gape number			
			A4