

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

2 W

DC- 18 GHz


SMA

COAXIAL ATTENUATOR

Issue  
04.aug.93

Page  
1 / 1

**DRAWING**



General tolerances: +/- 0.5 mm

**R F CHARACTERISTICS**

FREQUENCY RANGE : DC - 18 GHz  
 IMPEDANCE : 50 Ohms  
 ATTENUATION - NOMINAL : 45 dB

FREQUENCY	DC- 2 GHz	2 - 4 GHz	4 - 8 GHz	8 -12.4GHz	12.4- 18 GHz
V.S.W.R	<= 1.10	<= 1.15	<= 1.20	<= 1.25	<= 1.35
DEVIATION (dB)	+1.0 /-1.0	+1.0 /-1.0	+1.0 /-1.0	+1.0 /-1.0	+1.0 /-1.0


TEMPERATURE SENSITIVITY :  $4 \times 10^{-4} \text{ dB} / (\text{dB} \times ^\circ\text{C})$   
 PEAK POWER at 25°C (1µs,1%.) : 100 W  
 AVERAGE POWER at 25°C : 2 W

**MECHANICAL CHARACTERISTICS**

CONNECTORS : SMA male/female per MIL-C 39012  
 WEIGHT : < 10 g

**ENVIRONMENTAL CHARACTERISTICS**

OPERATING TEMPERATURE RANGE (°C) : -55 , +125  
 STORAGE TEMPERATURE RANGE (°C) : -55 , +125



QUALITY Dpt app  
 CREATION  
 PEN : CAT  
 EP :  
 Nom : KL  
 Date:11.dec.87

04.aug.93	New format	VE
ISSUE	REVISIONS	NAME

4412-9211