



REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	NEW			Henry	2014/9/30
△	Original Model C719-2			Henry	2023/10/16



RECOMMENDED P.C.B LAYOUT
COMPONENT SIDE(TOLERANCE ±0.05)

- PAD AREA
- CONNECTOR OUTLINE
- NO PATTERN AND VIA HOLE IN THIS AREA



TECHNICAL CHARACTERISTICS
 1.General Characteristics
 Dimensions:27.60LX18.70WX1.80H mm
 Weight:Approx 1.33g
 Durability:5,000 cycles min.
 2.Electrical Characteristics
 Contact resistance:50mΩ typical,
 100mΩ max
 Insulation resistance:>1000MΩ/500V
 DC
 3.Solderability
 Vapor phase:215°C,30sec.Max
 IR reflow:250°C,5sec.Max
 Manual soldering:370°C,3sec.Max
 4.Environmental Characteristics
 Operating temperature:-40°C~+85°C
 Operating humidity:10%~+95%RH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	SHELL	1	Stainless Steel	SMT area:Gold plated
3	DATA CONTACT	1	Copper Alloy	Contact area:Au 5u'/Au 30u'
4	HEART CAM	1	Hi-temp Thermoplastic	Black UL94V-0
5	COLL SPRING	1	SWP.	
6	CAM PIN	1	Stainless Steel	

Unless otherwise specified, other tolerance are:

X	±0.35	X'	±5'
X.X	±0.25	X.X'	±4'
X.XX	±0.15	X.XX'	±3'
X.XXX	±0.10	X.XXX'	±2'

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **SIM Card Connector**
 MODEL NO: **MUP-C7019-02**
 TYPE: **Without post/6pin**

PROJ.	UNIT	SCALE	DRAWN	DWG NO.:
	mm	1:1	Henry Sep.30.2014	DWG-C7019-02-01
CUSTOMER DRAWING			CHECKED	SHEET
			Simon Sep.30.2014	1/1
			APPROVAL	REVISION
				2

