



Electrical Specifications

Stop Band Frequency: 791~821MHz
Stop Band Attenuation: ≥45dB
Pass Band Frequency:
DC~771MHz & 841~2200MHz
Pass Band Insertion Loss: ≤1.5dB
Pass Band VSWR: ≤1.5:1
Impedance: 50 Ohms
Power Handling: 50W

Mechanical

Mounting Method: Thru Holes
Connector Type: N-Male/ N-Female
Dimensions: 239 x 88.5 x 28 mm

Environmental

Operating Temperature: -45°C to +85°C
Storage Temperature: -55°C to +95°C
Shock: 20 G. 11ms
Vibration: 20 G. 5 to 200 Hz

Outline Drawing:

