



Recommended PCB Layout  
(Top View)

**Materials and Finish**

Housing Material-  
PBT Thermoplastic  
UL 94V-0 Rated  
Color: Black

Contact Material-  
Phosphor Bronze

Contact Plating Options-  
Standard: 0.0001" Nickel  
Plating, Selective Plating  
Gold Flash on Contact  
Area, tin plated  
on termination end

50: 0.0001" Nickel Plating,  
Selective Plating 0.000050"  
Gold on Contact Area to  
Comply with FCC Requirements  
Under No. 47 C.F.R. Part 68,  
Subpart F  
Tin plated on termination end

**Electrical Characteristics**

Current Rating-  
1.5 Amps

Voltage Rating-  
125V DC

Insulation Resistance-  
500 Megohms Min.

Dielectric Withstanding Voltage-  
1000V rms, 60Hz

Contact Resistance-  
20 milliohms Max.

Operating Temperature-  
-40°C to +85°C

Part Number	Contact Area Plating Finish
GDLX-N-64	Gold Flash (standard)
GDLX-N-64-50	50u" Gold (-50 option)

Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise



REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	05/19/05	New Drawing	R. Aguirre	H. MA	R. Aguirre	05/16/05
A2	05/12/10	ECO #10-025	S. Vien	H. MA		
A3	11/06/13	ECO #13-084	W. Cook	H. MA		
A4	04/15/15	ECO #15-001	H. MA	C. Furumasu		
A5	05/19/17	ECO #17-014	H. MA	C. Furumasu		

**GDLX-N-64**

Modular Jack, Right angle, RoHS Compliant

6 Pos, 4 Contacts, non-shielded

