





6	7	8
版本	变更内容	工程确认 日期



TOLERANCE:  $\pm 0.05$   
RECOMMENDED PCB LAYOUT  
(TOP VIEW)



Ordering Information  
 YTC-1PH20 - XX - XX - AXX1 - X - X - X  
 No. Of Pins Per Row: 01~40  
 Standard Plating: 01=Gold Flash, 02=Gold 3U, 11=Plating Tin  
 Pin Length: 001=4.0/2.8, 002=5.84/2.8  
 Insulation Material: P=PBT, T=NL6T, L=LCP  
 Contact Material: B=Brass, P=Phone, Bronze  
 Packing: A=Pe Bag, B=Box, D=Tube  
 XX=Select Plating

Item	A	B
Standard	4.0	2.8
Select		

SPECIFICATIONS

- Current Rating: 2AMP
- Contact Resistance: 20MΩ Max
- Insulation Resistance: 1000MΩ Min
- Dielectric Withstanding : 500V AC
- Temperature Range: -40℃~+105℃
- Material:  
Contact Material: Brass  
Insulation Material: Polyester、UL94V-0 PBT

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD	页码 (SHEET)	1/1	单位(UNIT): MM
	版本 (REV)	A1	比例(SCALE)
品名 (ITEM NO)	2.00MM PIN HEADER SINGLE ROWS DIP TYPE BASE 2.00H CONNECTOR	日期 (DATE)	2021.10.12
料号 (PART NO)	YTC-1PH20-XXXX-SXX1-XXX	设计 (DESIGN)	LUO
图号 (DWG NO)	PH2.0	审核 (CHECKED)	ROGER LI
		核准 (APPROVED)	ROC ZHAO

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com