


✓ 54/7410 011054
 ✓ 54H/74H10 011058
 ✓ 54S/74S10 011059
 ✓ 54LS/74LS10 011057

TRIPLE 3-INPUT NAND GATE


CONNECTION DIAGRAMS
PINOUT A



ORDERING CODE: See Section 9

PKGS	PIN OUT	COMMERCIAL GRADE	MILITARY GRADE	PKG TYPE
		V _{CC} = +5.0 V ±5%, T _A = 0° C to +70° C	V _{CC} = +5.0 V ±10%, T _A = -55° C to +125° C	
Plastic DIP (P)	A	7410PC, 74H10PC 74S10PC, 74LS10PC		9A
Ceramic DIP (D)	A	7410DC, 74H10DC 74S10DC, 74LS10DC	5410DM, 54H10DM 54S10DM, 54LS10DM	6A
Flatpak (F)	A	74S10FC, 74LS10FC	54S10FM, 54LS10FM	3I
	B	7410FC, 74H10FC	5410FM, 54H10FM	

PINOUT B



INPUT LOADING/FAN-OUT: See Section 3 for U.L. definitions

PINS	54/74 (U.L.) HIGH/LOW	54/74H (U.L.) HIGH/LOW	54/74S (U.L.) HIGH/LOW	54/74LS (U.L.) HIGH/LOW
Inputs	1.0/1.0	1.25/1.25	1.25/1.25	0.5/0.25
Outputs	20/10	12.5/12.5	25/12.5	10/5.0 (2.5)

DC AND AC CHARACTERISTICS: See Section 3*

SYMBOL	PARAMETER	54/74		54/74H		54/74S		54/74LS		UNITS	CONDITIONS	
		Min	Max	Min	Max	Min	Max	Min	Max		V _{IN} = Gnd	V _{CC} = Max
I _{CC} H	Power Supply	6.0		12.6		12		1.2		mA	V _{IN} = Gnd	V _{CC} = Max
I _{CC} L	Current	16.5		30		27		3.3			V _{IN} = Open	
t _{PLH}	Propagation Delay	22		10		2.0 4.5		15		ns	Fig. 3-1, 3-4	
t _{PHL}		15		10		2.0 5.0		15				

*DC limits apply over operating temperature range; AC limits apply at T_A = +25° C and V_{CC} = +5.0 V.