

2 W

DC- 8 GHz


SMC

COAXIAL ATTENUATOR

issue
15. jul. 93

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 8 GHz
 IMPEDANCE : 50 Ohms
 ATTENUATION - NOMINAL : 10 dB

FREQUENCY	DC- 4 GHz	4 - 8 GHz
V.S.W.R	<= 1.15	<= 1.30
DEVIATION (dB)	+0.4 / - 0.4	+0.5 / - 0.5

TEMPERATURE SENSITIVITY : $4 \times 10^{-4} \frac{\text{dB}}{\text{dB} \times ^\circ\text{C}}$
 PEAK POWER at 25°C (1µs, 1%.) : 100 W
 AVERAGE POWER at 25°C : 2 W


MECHANICAL CHARACTERISTICS

CONNECTORS : SMC male/female per MIL-C 39012
 WEIGHT : < 5 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
 STORAGE TEMPERATURE RANGE (°C) : -55 , +125

Power derating
Versus temperature



This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

QUALITY Dpt app. _____		
CREATION PEN : CAT		
EP : -----		
Nom : KL	15. jul. 93	New issue
Date: 13. apr. 90	ISSUE	REVISIONS

RADIAL[®]

101. Philibert Hoffmann - Z.I Ouest -	Phone: 33.1.49353535 Fax : 33.1.48546363
93116 ROSNY/BOIS Cedex-FRANCE	Tlx RADIA 235220F

4112-9211