





BNC ATTENUATOR 20 DB 4 GHZ 2W

PAGE 1/2 ISSUE 17-07-15A SERIES ATTENUATOR PART NUMBER R414420150





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD OVER NICKEL
Female center contact Outer contact Insulator	BERYLLIUM COPPER BRASS PTFE	GOLD OVER NICKEL NICKEL
Gasket Substrate	SILICONE RUBBER ALUMINA CERAMIC	
Resistor Others parts	THIN FILM -	-



Technical Data Sheet

BNC ATTENUATOR 20 DB 4 GHZ 2W

PAGE 2/2	ISSUE 17-07-15A	SERIES ATTENUATOR	PART NUMBER R414420150
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

DC - 4 GHz	
50	Ω
20	dB
50	W
2	W (Free Air Cooled)
	W (Conduction Cooled)
	50 20 50


MECHANICAL CHARACTERISTICS

Connectors	BNC	Male Female	MIL-C 39012
Weight	26,9000 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS