




**Product:** [REVConnect CAT6+ Jacks](#)

REVConnect CAT6+ UTP Modular Jack, T568 A/B



## Product Description

REVConnect CAT6+ Jacks are available in several colors and packaging quantities.

## Technical Specifications

### Product Overview

Suitable Applications:	2400, 3600, 4800 Systems, TIA Category 6, ISO Class E, 1GBASE-T
------------------------	---

### Physical Characteristics (Overall)

Height:	0.94 in
Width:	0.64 in
Depth:	1.337 in
Wiring Scheme:	T568A/B
Packaging:	Individually packaged in a plastic bag.
Weight:	0.016 lbs

## Connectors

### Materials

Description	Material	Type
Front Connection	Copper Clad Flexible PCB, 50µin Gold plated contacts over Nickel	RJ45
Rear Connection	Copper alloy, Gold plated contacts over Nickel	REVConnect
Connector Body	PBT glass reinforced UL94V-0	

### Electrical Characteristics

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute (Signals to Ground)
Current Rating:	1.300 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm
Termination Resistance:	2.5 mOhm

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

Footprint/Type:	REVConnect
Tool Compatibility:	REVConnect Termination Tool (p/n RVUTT01)
Plug /Jack Compatibility:	RJ45, RJ11
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection

Termination Rear Connection Durability:	20 cycles
Cable/Connector Retention:	15 lbs.
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

## Standards

UL Rating:	UL94V-0
Data Category:	Category 6
TIA/EIA Compliance:	Category 6 - TIA 568.2-D, ISO/IEC 11801-1, TIA TSB-5021
IEEE Compliance:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBaseTTM (up to 100W)
Other Specification:	UL 1863, IEC 60603-7, ANSI/TIA 1096-A (formerly FCC Part 68-F)

## Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL2043 Air Handling Spaces
Safety Listing:	c(UL)us Listed

## Related Part Numbers

Related Parts:	Compatible with KeyConnect Faceplates, Adapters, Boxes and Patch Panels
----------------	---

## Variants

Item #	Color	Packaging
RV6MJKUAL-B24	Almond	Bulk Pack (24)
RV6MJKUAL-S1	Almond	Single Pack
RV6MJKUBK-B24	Black	Bulk Pack (24)
RV6MJKUBK-S1	Black	Single Pack
RV6MJKUBL-B24	Blue	Bulk Pack (24)
RV6MJKUBL-S1	Blue	Single Pack
RV6MJKUBR-B24	Brown	Bulk Pack (24)
RV6MJKUBR-S1	Brown	Single Pack
RV6MJKUGY-B24	Gray	Bulk Pack (24)
RV6MJKUGY-S1	Gray	Single Pack
RV6MJKUGN-B24	Green	Bulk Pack (24)
RV6MJKUGN-S1	Green	Single Pack
RV6MJKUIV-B24	Ivory	Bulk Pack (24)
RV6MJKUIV-S1	Ivory	Single Pack
RV6MJKUOR-B24	Orange	Bulk Pack (24)
RV6MJKUOR-S1	Orange	Single Pack
RV6MJKUPR-B24	Purple	Bulk Pack (24)
RV6MJKUPR-S1	Purple	Single Pack
RV6MJKURD-B24	Red	Bulk Pack (24)
RV6MJKURD-S1	Red	Single Pack
RV6MJKUEW-B24	White	Bulk Pack (24)
RV6MJKUYL-B24	Yellow	Bulk Pack (24)
RV6MJKUYL-S1	Yellow	Single Pack

## Product Notes

Included Parts:	1 Cat 6+ REVConnect Jack; 1 REVConnect Cable Manager and Cap; 1 Installation Guide
Notes:	Please see Installation Guide PX106434.

## History

Update and Revision:	Revision Number: 0.251 Revision Date: 03-04-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.