






NEX10 PUSH PULL MALE - N FEMALE ADAPTER

PAGE 1/2 ISSUE 23-08-17B SERIES ADAPTER PART NUMBER R191620007







All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	PLATING (μm)	
Body	BRASS.	BBR		
Center contact	BERYLLIUM COPPER	SILVER		
Outer contact	BERYLLIUM COPPER	SILVER		
Insulator	PTFE			
Gasket	SILICONE RUBBER			
Others parts	BRASS,BRONZE	BBR		
-	-	-		
-	-	-		



Technical Data Sheet

NEX10 PUSH PULL MALE - N FEMALE ADAPTER

PAGE 2/2	ISSUE 23-08-17B	SERIES ADAPTER	PART NUMBER R191620007
-----------------	------------------------	-------------------	-------------------------------

PACKAGING

Standard	Unit	Other
1	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

Impedance 50 Ο. Frequency 0-11 GHz VSWR 1.02 0.0150 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.05 RF leakage - (NA - F(GHz)) dB Maxi Veff Maxi 500

MECHANICAL CHARACTERISTICS

Center contact retention

 Axial force – Mating End
 27
 N mini

 Axial force – Opposite end
 27
 N mini

 Torque
 NA
 N.cm mini

Recommended torque

 $\begin{array}{ccc} \text{Mating life} & \textbf{100} & \text{Cycles mini} \\ \text{Weight} & \textbf{31.4220} & \text{g} \end{array}$

ENVIRONMENTAL

Operating -55~+125 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS
PIM3<=-123 dBm, 2 carriers of +43dBm