





TNC ATTENUATOR 10 DB 6 GHZ 150W

PAGE 1/2 ISSUE 02-02-21A SERIES PART NUMBER R422110040





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	PASSIVATED.
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINIUM NITRIDE	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





TNC ATTENUATOR 10 DB 6 GHZ 150W

PAGE <b>2/2</b>	ISSUE <b>02-02-21A</b>	SERIES ATTENUATOR	PART NUMBER <b>R422110040</b>
-----------------	------------------------	----------------------	-------------------------------

# **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 2.5	2.5 - 6
V.S.W.R (≤)	1.25	1.25
Deviation(±dB)	1	1

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
Nominal Attenuation	10	dB
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	150	W (Free Air Cooled)
		W (Conduction Cooled)


# MECHANICAL CHARACTERISTICS

Connectors	TNC	Male Female	MIL C39012
Weight	1845,32	g	

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

# Power derating Versus temperature



# SPECIFICATION

#### **OTHER CHARACTERISTICS**