

SPEC	NoR	ED-19P006B	
SPEC	No.	E ED-19P006B	

ISSUE: March 18, 2021

TO;

# SPECIFICATIONS

		Product Name	PHOTOCOUPLER	
		######################################	_	
		Model No.	PC357	
		【Business dealin	g name : PC357N**000F】	
	This specifical After confirm Specifications	tion sheets and atta ation of the contents with approving sign	pages including the cover and a ched sheets shall be both side , please be sure to send back_ nature on each. contact us before issuing pure	copy. 1 copy of the
Accepted by:				
			Sharp Corporation	
			77.0	
By:		<del>-</del>	By: F. Kajoli	
Name:			Name: T. Kamiyoshi	
Title:			Title: Senior Manager	10 1 1 0
Date:			Electronic Components an	id Devices Account Div.
D.,,			Date: Mar. 18. 202/	
By: Name:			Chara Eulawama Camiaanduat	on Co. I td
Title:			Sharp Fukuyama Semiconduct	or Co., Lta.
Date:			By: Tourander	
			Name: T. Hiramatsu	
			Title: Division Manager	
			Sensor Business Expand	ing Div.
			Semiconductor Busines	ss Unit
			Date: Mar. 18 204	
			Reviewed by:	Prepared by:
			By: 6/1/c/cm	By: H. Janaka
			Name: H. Takakura	Name: H. Tanaka
			Title: Associate Manager	Title: Supervisor
			Date: / Yav, 18, 202/	Date: Mar. 18, 2021

## **SHARP**

# REPC357N\*\*000FCE

- 1. These specification sheets include materials protected under copyright of Sharp Corporation ("Sharp"). Please handle with great cares and do not reproduce or cause anyone to reproduce them without Sharp's consent.
- 2. When using this Sharp product, please observe the absolute maximum ratings, other conditions and instructions for use described in the specification sheets, as well as the precautions mentioned below.

Sharp assumes no responsibility for any damages resulting from use of the product which does not comply with absolute maximum ratings, other conditions and instructions for use included in the specification sheets, and the precautions mentioned below.

#### (Precautions)

- (1) In making catalogue or instruction manual based on the specification sheets, please verify the validity of the catalogue or instruction manuals after assembling Sharp products in customer's products at the responsibility of customer.
- (2) This Sharp product is designed for use in the following application areas;
  - Computers OA equipment Telecommunication equipment (Terminal) Measuring equipment
  - Tooling machines Audio visual equipment Home appliances

If the use of the Sharp product in the above application areas is for equipment listed in paragraphs (3) or (4), please be sure to observe the precautions given in those respective paragraphs.

- (3) Appropriate measures, such as fail-safe design and redundant design considering the safety design of the overall system and equipment, should be taken to ensure reliability and safety when Sharp product is used for equipment in responsibility of customer which demands high reliability and safety in function and precision, such as:
  - Transportation control and safety equipment (aircraft, train, automobile etc.)
  - Traffic signals Gas leakage sensor breakers Rescue and security equipment
  - Other safety equipment
- (4)Sharp product is designed for consumer goods and controlled as consumer goods in production and quality. Please do not use this product for equipment which require extremely high reliability and safety in function and precision, such as;
  - Space equipment Telecommunication equipment (for trunk lines)
  - Nuclear power control equipment Medical equipment
- (5) Please contact and consult with a Sharp sales representative if there are any question regarding interpretation of the above four paragraphs.
- 3. Disclaimer

The warranty period for Sharp product is one (1) year after shipment.

During the period, if there are any products problem, Sharp will repair (if applicable), replace or refund.

Except the above, both parties will discuss to cope with the problems.

The failed Sharp product after the above one (1) year period will be coped with by Sharp, provided that both parties shall discuss and determine on sharing responsibility based on the analysis results thereof subject to the above scope of warranty.

The warranty described herein is only for Sharp product itself which are purchased by or delivered to customer. Damages arising from Sharp product malfunction or failure shall be excepted.

Sharp will not be responsible for the Sharp product due to the malfunction or failures thereof which are caused by:

- (1) storage keep trouble during the inventory in the marketing channel.
- (2) intentional act, negligence or wrong/poor handling.
- (3) equipment which Sharp products are connected to or mounted in.
- (4) disassembling, reforming or changing Sharp products.
- (5) installation problem.
- (6) act of God or other disaster (natural disaster, fire, flood, etc.)
- (7) external factors (abnormal voltage, abnormal electromagnetic wave, fire, etc.)
- (8) special environment (factory, coastal areas, hotspring area, etc.)
- (9) phenomenon which cannot be foreseen based on the practical technologies at the time of shipment.
- (10) the factors not included in the product specification sheet.
- 4. Please contact and consult with a Sharp sales representative for any questions about Sharp product.



1. Application

This specification applies to the outline and characteristics of photocoupler Model No. PC357.

Outline 2. Refer to page 4.

Ratings and characteristics Refer to page 5 and 6.

Reliability Refer to page 7.

Outgoing inspection Refer to page 8.

#### Supplement

6.1 Isolation voltage shall be measured in the following method.

- (1) Short between anode to cathode on the primary side and between collector to emitter on the secondary side.
- (2) The dielectric withstanding tester with zero-cross circuit shall be used.
- (3) The wave form of applied voltage shall be a sine wave.
- 6.2 Package specifications Refer to page 9 and 10.

("O" mark indicates business dealing name of ordered product) 6.3 Collector current (I<sub>C</sub>) Delivery rank table

Ordered product	Business dealing name	Rank mark	$I_{C}$ (mA)
	PC357NJ0000F	with or without	2.5 to 30.0
	PC357N1J000F	A	4.0 to 8.0
	PC357N2J000F	В	6.5 to 13.0
	PC357N3J000F	С	10.0 to 20.0
	PC357N4J000F	D	15.0 to 30.0
	PC357N5J000F	A or B	4.0 to 13.0
	PC357N6J000F	B or C	6.5 to 20.0
	PC357N7J000F	C or D	10.0 to 30.0
	PC357N8J000F	A, B or C	4.0 to 20.0
	PC357N9J000F	B, C or D	6.5 to 30.0

Test conditions
I <sub>F</sub> =5mA V <sub>CE</sub> =5V Ta=25°C

6.4 This Model is approved by UL.

Approved Model No.: PC357

UL file No.: E64380

#### 6.5 About radiation resistant design

- (1) This product is not designed against irradiation.
- (2) This product is assembled with electrical input and output.
- (3) This product incorporates non-coherent light emitting diode.

#### 6.6 ODS materials

- (1) This product shall not contain the following materials.
- (2) Also, the following materials shall not be used in the production process for this product.

Materials for ODS : CFC<sub>S</sub>, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methyl chloroform)

#### 6.7 Specified brominated flame retardants

Specified brominated flame retardants (PBB and PBDE) are not used in this device at all.



#### 6.8 Compliance with each regulation

- (1) This product complies with EU RoHS Directive (2011/65/EU) and Commission Delegated Directive (EU)2015/863.
- (2) Content of six substances specified in Management Methods for Control of Pollution Caused by Electronic Information Products Regulation (Chinese: 电子信息产品污染控制管理办法).

Marking Styles for the Names and Contents of the Hazardous Substances

		•	Hazardo	us Substances		
Category	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent chromium (Cr <sup>6+</sup> )	Polybrominated biphenyls (PBB)	Polybrominated diphenyl ethers (PBDE)
Photocoupler	0	0	0	0	0	0

This table is prepared in accordance with the provisions of SJ/T 11364.


 $\circ$ : Indicates that said hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement of GB/T 26572.


#### 7. Notes


Precautions for photocouplers : Attachment-1

# REPC357N\*\*000FCE

#### 2. Outline







- \*1 Date code: 3 digit indication according to production year, month and day
- \*2 Factory identification mark is as follows.

H: YONGYAO ENSEI ELECTRONICS (SHANGQIU) CO., LTD. (CHINA products)

\*3 Burr of resin max. 0.2 mm

Pin material: Copper Alloy

Pin finish : Palladium (Au flash plating)

Mark : Laser marking

A lead tip area and a part of a lead side area  $\,$ 

( area) are no-plating.

Product mass: Approx. 0.1g

UNIT: mm

PC357 Outline Dimensions

(Business dealing name : PC357N\*\*000F)

Name



#### 3. Ratings and characteristics

### 3.1 Absolute maximum ratings

Ta=25°C

		Parameter	Symbol	Rating	Unit
	*1 Forward current		$I_F$	50	mA
Input	*2	Peak forward current	$I_{FM}$	1	A
Inf		Reverse voltage	$V_R$	6	V
	*1	Power dissipation	P	70	mW
		Collector-emitter voltage	$V_{\text{CEO}}$	80	V
Output		Emitter-collector voltage	$V_{ECO}$	6	V
Ont		Collector current	$I_{C}$	50	mA
	*1	Collector power dissipation	$P_{\rm C}$	150	mW
	*1	Total power dissipation	P <sub>tot</sub>	170	mW
		Operating temperature	$T_{opr}$	-30 to +100	$^{\circ}\mathrm{C}$
		Storage temperature	$T_{\text{stg}}$	-40 to +125	$^{\circ}\mathrm{C}$
	*3	Isolation voltage	$V_{iso(rms)}$	3.75	kV
	*4	Soldering temperature	T <sub>sol</sub>	260	°C

<sup>\*1</sup> The dealing factors of absolute maximum ratings due to ambient temperature are shown in Fig. 1 to 4.

#### 3.2 Electro-optical characteristics

Ta=25°C


	Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
	Forward voltage	$V_{\rm F}$	I <sub>F</sub> =20mA	-	1.2	1.4	V
Input	Reverse current	$I_R$	V <sub>R</sub> =4V	-	-	10	μΑ
	Terminal capacitance	$C_t$	V=0, f=1kHz	-	30	250	pF
	Dark current	$I_{CEO}$	$V_{CE}=50V, I_{F}=0$	-	ı	100	nA
Output	Collector-emitter breakdown voltage	BV <sub>CEO</sub>	I <sub>C</sub> =0.1mA, I <sub>F</sub> =0	80	-	-	V
	Emitter-collector breakdown voltage	BV <sub>ECO</sub>	I <sub>E</sub> =10μA, I <sub>F</sub> =0	6	-	-	V
S	Collector current	$I_{\rm C}$	$I_F=5mA, V_{CE}=5V$	2.5	5	30	mA
Transfer characteristics	Collector-emitter saturation voltage	V <sub>CE(sat)</sub>	I <sub>F</sub> =20mA, I <sub>C</sub> =1mA	-	0.1	0.2	V
hara	Isolation resistance	R <sub>ISO</sub>	DC500V, 40 to 60%RH	5×10 <sup>10</sup>	1011	-	Ω
ferc	Floating capacitance	$C_{\rm f}$	V=0, f=1MHz	-	0.6	1.0	pF
rans	Response time (Rise)	t <sub>r</sub>	V <sub>CE</sub> =2V, I <sub>C</sub> =2mA,	-	4	18	μs
L	Response time (Fall)	t <sub>f</sub>	$R_L=100\Omega$	-	3	18	μs


<sup>\*2</sup> Pulse width ≤ 100 µs, Duty ratio : 0.001 (Refer to Fig. 5)


<sup>\*3</sup> AC for 1 min, 40 to 60%RH, f=60Hz


<sup>\*4</sup> For 10 s

# RPC357N\*\*000FICE









Pulse width  $\leq 100 \mu s$  $Ta = 25^{\circ}C$ 2000 Peak forward current  $I_{FM}(mA)$ 1000 500 200 100 50 20 10 10<sup>-3</sup> 10 -2 10 .0 10 -1 Duty ratio

(Fig. 5) Peak forward current vs. duty ratio




#### 4. Reliability

The reliability of products shall satisfy items listed below.

Confidence level: 90% LTPD: 10 or 20

		· · · · · · · · · · · · · · · · · · ·	
Test Items	Test Conditions *1	Failure Judgment Criteria	Samples (n) Defective(C)
Solderability	245 ± 3°C, 5 s	*2	n=11, C=0
Soldering heat *3	(Flow soldering) 260°C, 10 s		n=11, C=0
Soldering heat *3	(Soldering by hand) 400°C, 3 s		n=11, C=0
Terminal strength (Bending) *4	Weight: 1N, 1 time/each terminal	$V_F > U \times 1.2$	n=11, C=0
Mechanical shock	$15 \text{km/s}^2$ , 0.5ms, $3 \text{ times/} \pm X$ , $\pm Y$ , $\pm Z$ direction	$ \begin{array}{ccc} I_R &> U \times 2 \\ I_{CEO} &> U \times 2 \end{array} $	n=11, C=0
Variable frequency vibration	100 to 2000 to 100Hz/4min 200m/s <sup>2</sup> 4 times/ X, Y, Z direction	$ \begin{array}{c} I_C & < L \times 0.7 \\ V_{CE(sat)} & > U \times 1.2 \end{array} $	n=11, C=0
Temperature cycling	1 cycle -40°C to +125°C (30min) (30min) 20 cycles test		n=22, C=0
High temp. and high humidity storage *5	+85°C, 85%RH, 500h		n=22, C=0
High temp. storage	+125°C, 1000h	U: Upper specification limit L: Lower specification limit	n=22, C=0
Low temp. storage	-40°C, 1000h	12. Lower specification limit	n=22, C=0
Operation life	I <sub>F</sub> =50mA, P <sub>tot</sub> =170mW, Ta=25°C, 1000h		n=22, C=0

- \*1 Test method, conforms to EIAJ ED 4701.
- \*2 The product whose not-soldered area is more than 5% for all of the dipped area and/or whose pinholes or voids are concentrated on one place shall be judged defect.
- \*3 It is evaluated due to the temperature profile in attachment-1.
- \*4 Terminal bending direction is shown below.
- \*5 It is evaluated after washing by specified solvent in attachment-1.



\*These test results are sampling examples from a specific lot for reference purpose only, and do not constitute any warranty or assurance in connection with the products.



#### 5. Outgoing inspection

#### 5.1 Inspection items

(1) Electrical characteristics

 $V_F,\,I_R,\,I_{CEO},\,V_{CE(sat)},\,I_C,\,R_{ISO},\,V_{iso}$ 

(2) Appearance

#### 5.2 Sampling method and Inspection level

A single sampling plan, normal inspection level II based on ISO 2859 is applied.

The AQL according to the inspection items are shown below.

Defect	Inspection item	AQL(%)
Major defect	Electrical characteristics Unreadable marking	0.065
Minor defect	Appearance defect except the above mentioned.	0.25



#### 6.2 Package specifications

#### 6.2.1 Taping conditions

(1) Tape structure and Dimensions (Refer to below.)

The carrier tape has the heat pressed structure of A-PET or PS material carries tape of protect against static electricity and three layers cover tape (PET material base).

(2) Reel structure and Dimensions (Refer to page 10.)

The taping reel shall be of plastic (PS material).

(3) Direction of product insertion (Refer to page 10.)

(4) Joint of tape

The cover tape and carrier tape in one reel shall be joint less.

(5) To repair failure-taped devices, cutting a bottom of carrier tape or a cover tape with a cutter.

After replacing the cut portion shall be sealed with adhesive tape.

#### 6.2.2 Adhesiveness of cover tape

• The exfoliation force between carrier tape and cover tape shall be  $0.2\,\mathrm{N}$  to  $0.7\,\mathrm{N}$  for the angle  $160^\circ$  to  $180^\circ$ .

#### 6.2.3 Rolling method and quantity

• Wind the tape back on the reel so that the cover tape will be outside the tape.

Attach more than 20 cm of blank tape to the trailer and the leader of the tape and fix the both ends with adhesive tape. One reel basically shall contain 3,000 pcs.

6.2.4 Outer packing appearance (Refer to page 10.)

#### 6.2.5 Marking

- The label with following information shall be pasted at appointed place of the outer packing case.
  - \* Model No. \*(Business dealing name) \* Lot No. \* Quantity
  - \*Country of origin \*Company name \*Inspection date specified


#### 6.2.6 Storage condition

• Taped products shall be stored at the temperature 5°C to 30°C and the humidity 70%RH or less away from direct sunlight.

#### 6.2.7 Safety protection during shipping

• There shall be no deformation of component or degradation of electrical characteristics due to shipping.

#### Carrier tape structure and Dimensions




Dimensions list (Unit:mm)

A	В	С	D	Е	F	G	Н	I	J	K
±0.3	±0.05	±0.10	±0.1	±0.05	±0.1	+0.1 -0.0		±0.05	±0.1	±0.1
12.0	5.50	1.75	8.0	2.00	4.0	φ1.5	7.4	0.30	3.1	4.0

# R PC357N\*\*000FICE


#### Reel structure and Dimensions





Dimensions list	(Unit: mm)
Difficusions list	(Ont. mi

a	b	С
(380)	13.4±1.0	φ80.0±1.0
d	e	f
φ13.0±0.2	φ21.0±0.8	2.0±0.5


### Direction of product insertion







### Outer packing appearance





#### Precautions for Photocouplers

1. Cleaning

(1) Solvent cleaning : Solvent temperature 45°C or less

Immersion for 3 min or less

(2) Ultrasonic cleaning : The effect to device by ultrasonic cleaning differs by cleaning bath size, ultrasonic power output,

cleaning time, PCB size or device mounting condition etc. Please test it in actual using condition

and confirm that any defect doesn't occur before starting the ultrasonic cleaning.

(3) Applicable solvent : Ethyl alcohol, Methyl alcohol, Isopropyl alcohol

When the other solvent is used, there are cases that the packaging resin is eroded.

Please use the other solvent after thorough confirmation is performed in actual using condition.

#### 2. Circuit design

(1) The LED used in the Photocoupler generally decreases the light emission power by operation. In case of long operation time, please design the circuit in consideration of the degradation of the light emission power of the LED. (50%/5years)

(2) There are cases that the deviation of the CTR and the degradation of the relative light emission power of the LED increase when the setting value of I<sub>F</sub> is less than 1.0mA. Please design the circuit in consideration of this point.

#### 3. Precautions for Soldering


(1) In the case of flow soldering (Whole dipping is possible.)

It is recommended that flow soldering should be at 260°C or less for 10 s or less (Pre-heating: 100 to 150°C, 30 to 80s).

(2 times or less)

#### (2) If solder reflow:

It is recommended to be done at the temperature and the time within the temperature profile as shown in the figure below. (2 times or less)



#### (3) In the case of hand soldering

What is done on the following condition is recommended. (2 times or less)

Soldering iron temperature : 400°C or less Time : 3s or less

#### (4) Other precautions

Depending on equipment and soldering conditions (temperature, Using solder etc.), the effect to the device and the PCB is different. Please confirm that there is no problem on the actual use conditions in advance.