



UABS2 THRU UABS10


Voltage Range - 200 to 1000 V olts Current - 0.8/1.0 Ampere

GLASS PASSIVATED FAST RECOVERY BRIDGE RECTIFIERS

Features


- ◆ Ideal for printed circuit board
- ◆ Reliable low cost construction utilizing molded plastic technique
- ◆ High temperature soldering guaranteed: 260°/10 seconds at 5 lbs., (2.3kg) tension
- ◆ Small size, simple installation
- ◆ High surge current capability
- ◆ Glass passivated chip junction

ABS **RoHS**
COMPLIANT



Mechanical Data

Case : JEDEC ABS Molded plastic body
Terminals : Solder plated, solderable per MIL-STD-750, Method 2026
Polarity : Polarity symbol marking on body
Mounting Position : Any
Weight : 0.003 ounce, 0.098 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD UABS2	MDD UABS4	MDD UABS6	MDD UABS8	MDD UABS10	UNITS
Marking Code							
Maximum repetitive peak reverse voltage	V_{RRM}	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	200	400	600	800	1000	V
Maximum average forward rectified current On glass-epoxy P.C.B.(Note1) On aluminum substrate(Note2)	$I_{F(AV)}$	0.8 1.0					A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	30					A
Maximum instantaneous forward voltage drop per leg at 0.4A	V_F	1.0	1.4	1.7		V	
Maximum DC reverse current at rated DC blocking voltage $T_A=25^\circ C$ $T_A=100^\circ C$	I_R	5 500					μA μA
Typical thermal resistance(NOTE 3)	$R_{\theta JL}$ $R_{\theta JA}$	25 75					$^\circ C/W$
Maximum reverse recovery time (NOTE 4)	t_{rr}	50		75		ns	
Operating temperature range	T_J	-55 to +150					$^\circ C$
storage temperature range	T_{STG}	-55 to +150					$^\circ C$

NOTES:1. On glass epoxy P.C.B. mounted on 0.05x0.05"(1.3x1.3mm) pads.
 2. On aluminum substrate P.C.B. with an area of 0.8"x0.8"(20x20mm) mounted on 0.05X0.05"(1.3X1.3mm) solder pad.
 3. Thermal resistance from junction to ambient and junction to lead mounted on P.C.B. with 0.2X0.2"(5X5mm) copper pads.
 4. Reverse recovery condition $I_F=0.5A, I_R=1.0A, I_{rr}=0.25A$.



UABS2 THRU UABS10

Voltage Range - 200 to 1000 V olts Current - 0.8/1.0 Ampere

Ratings And Characteristic Curves

FIG.1 FORWARD DERATING CURVE




FIG.2 PEAK FORWARD SURGE CURRENT




FIG.3 TYPICAL FORWARD CHARACTERISTICS





FIG.4 TYPICAL REVERSE CHARACTERISTICS




The curve above is for reference only.



UABS2 THRU UABS10

Voltage Range - 200 to 1000 V olts Current - 0.8/1.0 Ampere

Suggested Pad Layout



Dim	Min
P1	5.72
P2	4.00
Q1	1.00
Q2	0.90