




**SPECIFICATIONS**  
 Current Rating: 3Amps  
 Insulation Resistance: 1000M $\Omega$  Min  
 Contact Resistance: 20M $\Omega$  Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Copper Alloy  
 Standard: PBT  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 200°C for 30-60 seconds (220°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PH2.54-01-01PZS	1	0.00	2.54
PH2.54-01-02PZS	2	2.54	5.08
PH2.54-01-03PZS	3	5.08	7.62
PH2.54-01-04PZS	4	7.62	10.16
PH2.54-01-05PZS	5	10.16	12.70
PH2.54-01-06PZS	6	12.70	15.24
PH2.54-01-07PZS	7	15.24	17.78
PH2.54-01-08PZS	8	17.78	20.32
PH2.54-01-09PZS	9	20.32	22.86
.....	.....	.....	.....
PH2.54-01-40PZS	40	(PIN-1)X2.54	(PIN)X2.54



PART NUMBER DESCRIPTION:

PH2.54-01-NPZS

$\uparrow$  (D=单排; S=双排)  
 $\uparrow$  (Z=直脚; W=弯脚)  
 $\uparrow$  (PIN数量; 01.....40PIN)  
 $\uparrow$  (排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 2xNPin 180度 PC3.0 PA6.0 PB2.5 L11.5 PBT	
DECIMALS:	ANGLES:		PAR PH2.54-01-NPZS	
X. $\pm 0.30$	X° $\pm 5'$		DWN	
X.X $\pm 0.20$	X.X° $\pm 1'$		CHKD	
X.XX $\pm 0.10$	X.XX° $\pm 0.5'$	APVD		
CUSTOMER COPY		SCALE N:A	UNIT:MM	
		SIZE:A4	SHEET:1F1	
			REV:A	