



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds (260°C for 5 seconds)


P/N	PIN	DIM.A	DIM.B
PH2.0-01-01PZS	1	0.00	2.00
PH2.0-01-02PZS	2	2.00	4.00
PH2.0-01-03PZS	3	4.00	6.00
PH2.0-01-04PZS	4	6.00	8.00
PH2.0-01-05PZS	5	8.00	10.00
PH2.0-01-06PZS	6	10.00	12.00
PH2.0-01-07PZS	7	12.00	14.00
PH2.0-01-08PZS	8	14.00	16.00
PH2.0-01-09PZS	9	16.00	18.00
.....
PH2.0-01-40PZS	40	(PIN-1)x2.0	(PIN)x2.0



PART NUMBER DESCRIPTION:

PH2.0-01-NPZS

- (D=单排; S=双排)
- (Z=直脚; W=弯脚)
- (PIN数量; 01.....40PIN)
- (排针开关)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.0PH H2.0 2xnPin 180度 PC2.8 PA3.9 PB2.0 L8.7 6T	
DECIMALS:	ANGLES:		PAR PH2.0-01-NPZS	
X.±0.30	X°±5'		DWN	
X.X±0.25	X.X°±1'		CHKD	
X.XX±0.20	X.XX°±0.5'	APVD		
CUSTOMER COPY		SCALE N:A	UNIT:MM	
		SIZE:A4	SHEET:1F1	
			REV:A	