

注：本板为禁止传输、复制、编辑文件，以及用其内容进行交流

REV	ECN NO.	CONTENT	CHK	DATE
-----	---------	---------	-----	------

NOTES:
UL Standard

- 1.Rating voltage/current: 300V/8A
- 2.withstanding voltage: AC2000V/1min
- 3.Torque value: M2.0, 1.77Lbin
- 4.Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

2. Torque value: M2, 0.2Nm
- 3 wire range: 0.5~1.5mm²

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Clamp: Copper alloy (Ni Plated)
- 5.Screw 1: Steel (M2.0,Zn Plated)
- 6.Screw 2: Steel (M2.5,Zn Plated)

NOTES3:




- 1.Pitch: 3.81mm Poles: 02-24P
- 2.Stripping length: 6-7mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX15EDGKM - 381 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 01:常规颜色
灰色:GY 棕色:OE 02-99:
蓝色:BU 红色:RD 定制颜色
黑色:BK 透明色:T
绿色:GN 黄色:YW
透明色:T 白色:WE

A-Z其他定制
0-Y一字螺丝
1:S十字螺丝
2:PS平头十字螺丝
Cu:铜方块
Fe:铁方块



Pitch Range	In mm	Nominal Dimension	Range
-------------	-------	-------------------	-------

Over 6	Over 10	Over 30	Over 60	Over 100	Over 150	-	0.1/10
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150	<
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±2°

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	APP	DATE	SCALE	NAME
CKK	DATE	DATE	22.09.14	MM	MX15EDGKM-3.81-XXP
DATE	DATE	DATE		A4	
CXI MAIXU ELECTRONICS CO.,LTD 慈溪市迈旭电子有限公司					DWGNO.