



CIRCUIT DIAGRAM



P.C.B LAND DIMENSION

SPECIFICATION

1. Rating: DC 12V 50mA Max
2. Contact resistance: 100mΩ MAX
3. Insulation resistance: 100MΩ Min
4. Dielectric strength: 250VAC/min
5. Operating force: 250gf±50gf
6. Operating life: 500,000 cycles

REFERENCE DRAWING

UNSPECIFIED 未指定的公差	TOLERANCE	4	TAPE (脚空腔)	1	PI	
ANGULAR(角度)	±0.5°	3	CONTACT FORM(弹片)	1	SUS301	Ag plating
16 < L ≤ 63	±0.4	2	HOUSING(基座)	1	LCP	
4 < L ≤ 16	±0.3	1	TERMINAL(端子)	1	BRASS	Ag plating
L ≤ 4	±0.2		NO.(序号) PART NAME(部件名)	QTY(数量)	MATERIAL(材料)	REMARK(备注)



**D-SWITCH**  
东莞市德松电子有限公司  
D-SWITCH ELECTRONICS CO.,LTD

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	核准 APPROVED BY	比例尺 SCALE	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				A0		1:1		2023.02.24	赵华玲	DS-TV/CU12-C	XXXXXXX