

# APPROVAL SHEET

# **MULTILAYER CERAMIC DIPLEXER**

RFDIP Series - 1608(0603)- RoHS Compliance

Halogens Free Product

2.4 GHz & 5 GHz ISM Band RF Application

P/N: RFDIP1608060LW8D1T

\*Contents in this sheet are subject to change without prior notice.

## **FEATURES**


- 1. Miniature footprint: 1.6 X 0.8X 0.6 mm<sup>3</sup>
- 2. Low Insertion Loss
- 3. High attenuation on 2<sup>nd</sup> harmonic suppressed
- 4. LTCC process

# **APPLICATIONS**

- 1. ISM 2.4/ 5GHz band RF application
- 2. Wi-Fi 802.11a/b/g/n application

## **CONSTRUCTION**

Top view



PIN	Connection	PIN	Connection
1	High Band	4	GND
2	GND	5	ANT Port
3	Low Band	6	GND

## **DIMENSIONS**

Figure			Symbol	Dimension (mm)
	E			1.60 ± 0.15
		В	W	0.80 ± 0.15
		U	Т	0.60 ± 0.10
			А	0.175 ± 0.15
		Q	В	0.25 ± 0.15
			С	0.25 ± 0.15
	W	T	D	0.50 ± 0.15
Top view	Bottom view	Side view	E	0.20 ± 0.15



#### **ELECTRICAL CHARACTERISTICS**

Item	Specification		
Frequency range	2400~2500 MHz	4900~5950 MHz	
lacortion Loca	0.50 dB max. at +25 °C	0.60 dB max. at +25 °C	
Insertion Loss	0.60 dB max. at -40 ~ +85 ℃	0.70 dB max. at -40 ~ +85 °C	
		25 dB min. @ 860~960MHz	
	10 dB min. @3600~3750MHz	25 dB min. @ 1545~1605MHz	
	20 dB min. @4800~5000MHz	25 dB min. @ 1710~1990MHz	
Attenuation	20 dB min. @5000~5950MHz	30 dB min. @ 2170 MHz	
	10 dB min. @7200~7500MHz	10 dB min. @ 8100~8800 MHz	
	10 dB min. @9600~10000MHz	15 dB min. @ 8820~9800 MHz	
		25 dB min. @ 9800~11900 MHz	
Isolation	_	25 dB min. @ 4800~5000 MHz	
Return Loss	15 dB min.		
Moisture sensitivity levels	LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)		

# **Operating & Storage Condition (Component)**


Operation Temperature Range: -40 ~ +85 °C Storage Temperature Range: -40 ~ +85 ℃

# Storage Condition before Soldering (Included packaging material)


Storage Temperature Range: +5 ~ +40 °C Humidity: 30 to 70% relative humidity

# TYPICAL ELECTRICAL PERFORMANCE





# LAND PATTERN



Line width to be designed to match 50  $\,\Omega$  characteristic impedance, depending on PCB material and thickness.



# **RELIABILITY TEST**

Test item	Test condition / Test method	Specification
Solderability	*Solder bath temperature : 235 $\pm$ 5°C	At least 95% of a surface of each terminal
JIS C 0050-4.6	*Immersion time: 2 ± 0.5 sec	electrode must be covered by fresh solder.
JESD22-B102D	Solder : Sn3Ag0.5Cu for lead-free	
Resistance to soldering heat	*Preheating temperature: 120~150°C,	No mechanical damage.
JIS C 0050-5.4	1 minute.	Electrical specification shall satisfy the
	*Solder temperature : 270±5°C	descriptions in electrical characteristics under
	*Immersion time: 10±1 sec	the operational temperature range within -40
	Solder: Sn3Ag0.5Cu for lead-free	~ 85°C.
	Measurement to be made after keeping at	Loss of metallization on the edges of each
	room temperature for 24±2 hrs	electrode shall not exceed 25%.
Drop Test	*Height: 75 cm	No mechanical damage.
JIS C 0044	*Test Surface: Rigid surface of concrete or	Electrical specification shall satisfy the
Customer's specification.	steel.	descriptions in electrical characteristics under
	*Times: 6 surfaces for each units; 2 times for each side.	the operational temperature range within -40 ~ 85°C.
Vibration	*Frequency: 10Hz~55Hz~10Hz(1min)	No mechanical damage.
JIS C 0040	*Total amplitude : 1.5mm	Electrical specification shall satisfy the
	·	descriptions in electrical characteristics under
	*Test times: 6hrs.(Two hrs each in three	the operational temperature range within -40
	mutually perpendicular directions)	~ 85°C.
Adhesive Strength	*Pressurizing force :	No remarkable demand or remarkal of the
of Termination	5N(≤0603) ; 10N(>0603)	No remarkable damage or removal of the termination.
JIS C 0051- 7.4.3	*Test time: 10±1 sec	terrimation.
Bending test	The middle part of substrate shall be	No mechanical damage.
JIS C 0051- 7.4.1	pressurized by means of the pressurizing rod	Electrical specification shall satisfy the
	at a rate of about 1 mm/s per second until the	descriptions in electrical characteristics under
	deflection becomes 1mm/s and then pressure	the operational temperature range within -40
	shall be maintained for 5±1 sec.	~ 85°C.
	Measurement to be made after keeping at	
	room temperature for 24±2 hours	

Approvar sneet		
JIS C 0025	1. 30±3 minutes at -40°C±3°C, 2. 10~15 minutes at room temperature, 3. 30±3 minutes at +85°C±3°C, 4. 10~15 minutes at room temperature, Total 100 continuous cycles  Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Humidity (steady conditions) JIS C 0022	*Temperature: 85°C±2°C  *Test duration: 1000+24/-0 hours  Measurement to be made after keeping at room temperature for 24±2 hrs  *Humidity: 90% to 95% R.H.  *Temperature: 40±2°C  *Time: 1000+24/-0 hrs.	No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.  No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under
Low temperature JIS C 0020	Measurement to be made after keeping at room temperature for 24±2 hrs  300hrs measuring the first data then 1000hrs data  *Temperature: -40°C±2°C  *Test duration: 1000+24/-0 hours  Measurement to be made after keeping at room temperature for 24±2 hrs	the operational temperature range within -40 ~ 85°C.  No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.

## **SOLDERING CONDITION**

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

# **ORDERING CODE**

RF	DIP	160806	0	L	W8D1T
Walsin	Product	Dimension code	Unit of dimension	Application	Specification
RF	Code	Per 2 digits of Length,	0 : 0.1 mm	L :2.4GHz/5GHz	Design code
device	DIP : Diplexer	Width, Thickness:	1 : 1.0 mm		
		e.g. :			
		160806 =			
		Length 16,			
		Width 08,			
		Thickness 06			

Minimum Ordering Quantity: 4000 pcs per reel.

# **PACKAGING**




## Paper Tape specifications (unit :mm)

Index	Ao	Во	ΦD	Т	W
Dimension (mm)	0.975± 0.10	1.76 ±0.10	1.55 + 0.05	0.75± 0.10	$8.0 \pm 0.10$
Index	Е	F	Po	P1	P2
Dimension (mm)	1.75 ± 0.10	$3.50 \pm 0.05$	4.00 ± 0.10	$4.00\pm0.10$	$2.00\pm0.05$



#### **Reel dimensions**



Index	Α	В	С
Dimension (mm)	Ф178.0	Ф60.0	Ф13.0

Taping Quantity:4000 pieces per 7" reel

#### **CAUTION OF HANDLING**

#### **Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

#### Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
  - Products should be storage in the warehouse on the following conditions.

■ Temperature : +5 to +40°C

Humidity : 30 to 70% relative humidity

- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.