

MCMB-0624 Series

High Current Molded Power Inductors

FEATURES

- Powder iron core material
- Magnetically shielded, low EMI
- High current carrying capacity, Low core losses
- Frequency range up to 3MHz
- Operate temperature range -40° C $\sim +125^{\circ}$ C (Including self temp. rise)
- RoHS compliant





APPLICATIONS

- Voltage Regulator Module (VRM)
- Multi-phase regulators
- Point-of-load modules
- Smart phone POL modules
- SSD modules
- Notebook regulators
- Battery power systems
- Graphics cards
- Data networking and storage systems

Explanation of Part Number


MCMB -0624 -1R0 M T

1 2 3 4 5

- ♦ 1:Product Series:Metal Alloy Molding Power Inductor
- ♦ 2:Dimensions:
- ♦ 3: Initial inductance value: 1R0 = 1.0uH
- ♦ 4:Tolerance of Inductance:M:±20%
- ♦ 5:Packing:Tape Carrier Package



Dimensions: [mm]



Series	Α	В	С	D	E	I Тур.	Ј Тур.	Н Тур.
MCMB-0624	6.6±0.2	7.0±0.3	2.2±0.2	1.6±0.3	3.0±0.3	2.35	3.7	3.5

Electrical Properties:


Part Number	Inductance	DC Resistance	Saturation Current		Heat Rating Current	
	@100KHz,1V	Max.	Max.	Тур.	Max.	Тур.
Units	μH	mΩ	Α		Α	
Symbol	L	DCR	Isat		Irms	
MCMB-0624-R22MT	0.22±20%	3	24.0	30.0	19.0	21.0
MCMB-0624-R33MT	0.33±20%	4.1	19.6	24.5	16.0	18.0
MCMB-0624-R47MT	0.47±20%	5.1	16.0	20.0	13.5	15.0
MCMB-0624-R56MT	0.56±20%	6.5	13.6	17.0	11.5	13.0
MCMB-0624-R68MT	0.68±20%	7	12.8	16.0	10.5	12.0
MCMB-0624-1R0MT	1.0±20%	13.5	12.0	15.0	8.00	9.00
MCMB-0624-1R5MT	1.5±20%	20	10.8	13.5	7.00	8.20
MCMB-0624-2R2MT	2.2±20%	28	8.00	10.0	6.20	7.00
MCMB-0624-3R3MT	3.3±20%	39	6.40	8.00	4.80	5.50
MCMB-0624-4R7MT	4.7±20%	50	5.20	6.50	4.30	5.00
MCMB-0624-6R8MT	6.8±20%	70	4.80	6.00	3.20	4.00
MCMB-0624-100MT	10±20%	101	3.20	4.00	2.40	3.10
MCMB-0624-150MT	15±20%	160	2.64	3.30	2.00	2.50
MCMB-0624-220MT	22±20%	230	2.00	2.50	1.60	2.00

Notes


- %1: All test data is referenced to 20°C ambient;
- ※2: Rated current: Isat or Irms, whichever is smaller;
- 3: Isat(Typ): DC current at which the inductance drops approximate 30% from its value without current;
- *4: Isat(Max): DC current at which the inductance drops approximate 20% from its value without current;
- %5: Irms(Typ): DC current that causes the temperature rise (\triangle T =40°C) from 20°C ambient.
- %6: Irms(Max): DC current that causes the temperature rise (\triangle T =20°C) from 20°C ambient.
- ※7: Absolute maximum voltage 30VDC



TYPICAL ELECTRICAL CHARACTERISTICS










Reliability and Test Condition

Item	Specification and Requirement	Test Method		
item				
Solderability	The surface of terminal immersed shall	Solder heat proof:		
	be minimum of 95% covered with a new	1. Preheating: 160 ± 10 °C		
	coating of solder	2. Retention time: 245 ± 5 °C for 2 ± 0.5 seconds		
	Inductance change: Within ± 10%	1. Vibration frequency:		
		(10 Hz to 55 Hz to 10Hz) in 60 seconds as a period		
Vibration	Without mechanical damage such as	2. Vibration time:		
	break	Period cycled for 2 hours in each of 3 mutual		
		perpendicular directions.		
		3. Amplitude: 1.5 mm max.		
		1. Peak value: 100 G		
Shock	Inductance change: Within ±10% Without	2. Duration of pulse: 11ms		
	mechanical damage such as break	3. 3 times in each positive and negative direction of 3		
		mutual perpendicular directions		
Endurance Reli	<u> </u>			
Item	Specification and Requirement	Test Method		
	Inductance change: Within ± 10% Without distinct damage in appearance	Repeat 100 cycles as follow:		
		(-55 ± 2 °C; 30 ± 3 min)		
Thermal		→(Room temp., 5 min)		
Shock		\rightarrow (+125 ± 2 °C, 30 ± 3 min)		
		→ (Room temp., 5 min)		
		2. Recovery: 48 + 4 / -0 hours of recovery under the		
		standard condition after the test.		
High	Inductance change: Within ± 10%	1. Environment condition: 85 ± 2 ℃		
Temperature	Without distinct damage in appearance	Applied Current: Rated current		
Resistance	This are are are a series of the series of t	2. Duration: 1000 + 4 / -0 hours		
		1. Environment condition: 60 ± 2 ℃		
Humidity	Inductance change: Within ± 10%	Humidity: 90–95%		
Resistance	Without distinct damage in appearance	Applied Current: Rated current		
		2. Duration: 1000 + 4 / -0 hours		
Low	Inductance change: Within ± 10%	Store temperature:		
Temperature	Without distinct damage in appearance	-55 ± 2 °C,1000 + 4 / -0 hours		
Store	Tritiout distinct damage in appearance	-55 12 C,1000 1 47 -0 Hours		
High	Inductance change: Within ± 10%	Store temperature:		
Temperature		Store temperature: +125 ± 2 ℃,1000 + 4 / -0 hours		
Store	Without distinct damage in appearance	123 12 C, 1000 147-0 Hours		




Tape Packaging Dimensions



A0	В0	K0	t
7.2±0.10	7.5±0.10	3.6±0.15	0.31±0.05

Reel Dimensions



Packing Quantity:1000pcs/Reel



Recommended Soldering Technologies

(1) Re-flowing Profile

Preheat condition: 150 ~200 °C/60~180sec.


Allowed time above 217°C: 80~120sec.

Max temp: 260°C

Max time at max temp: 10 sec.

Solder paste: Sn/3.0Ag/0.5Cu

Allowed Reflow time: 2x max



(2) Iron Soldering Profile

Iron soldering power: Max.

30W Pre-heating: 150°C/60sec.

Soldering time: 3sec. Max.

Solder paste: Sn/3.0Ag/0.5Cu

Max.1 times for iron soldering

