

APPROVAL SHEET

RFCPL Series – 1608(0603) – RoHS Compliance

MULTILAYER CERAMIC COUPLER

Halogens Free Product

698 ~ 2690 MHz Working Frequency

P/N: RFCPL1608070P3T

*Contents in this sheet are subject to change without prior notice.



FEATURES


- 1. Miniature footprint: 1.6X 0.8 X 0.7 mm³
- 2. Low Insertion loss
- 3. High Isolation
- 4. LTCC process

APPLICATIONS

- 1. 698 ~ 2690 MHz Working Frequency
- 2. TDD_LTE/FDD_LTE RF applications
- 3. Bluetooth, Wireless LAN 802.11b/g/ n, HomeRF

CONSTRUCTION


Top view



If P1 is input port, the pin is defined as the table.					
PIN Connection PIN Connection					
1	Input	4	Termination		
2	GND	5	GND		
3	Output	6	Coupling		

If P3 is input port, the pin is defined as the table.				
PIN Connection PIN Connection				
1	Output	4	Coupling	
2	GND	5	GND	
3	Input	6	Termination	

DIMENSIONS





ELECTRICAL CHARACTERISTICS

RFCPL1608070P3T	Specification		
Frequency range	698 ~ 2690 MHz		
	0.20 dB max. (0.07 dB typ.) @ 698 ~ 960 MHz		
Insertion Loss at +25 °C	0.22 dB max. (0.11 dB typ.) @ 1710 ~ 2170 MHz		
	0.25 dB max. (0.11 dB typ.) @ 2300 ~ 2690 MHz		
	0.30 dB max. @ 698 ~ 960 MHz		
Insertion Loss at -40°C ~ +85°C	0.32 dB max. @ 1710 ~ 2170 MHz		
	0.35 dB max. @ 2300 ~ 2690 MHz		
	23.0 ~ 27.0 dB @ 698 ~ 915 MHz		
Coupling in BW	21.5 ~ 26.5 dB @ 1710 ~ 2025 MHz		
	22.5 ~ 27.5 dB @ 2300 ~ 2690 MHz		
Isolation	40 dB min. @ 698 ~ 2690 MHz		
Directivity in BW	20.0 dB min. @ 698 ~ 2690 MHz		
VSWR	1.45 max.		
Impedance	50 Ω		
Power Capacity	4W max.		
Moisture sensitivity levels	MSL is LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)		
HBM ESD	Pass 1KV on all pins (Base on AEC-Q200-002)		
MM ESD	Pass 200V (Base on EIA/JESD22-A115)		


Operating & Storage Condition (Component)


Operation Temperature Range: -40° C ~ $+85^{\circ}$ C Storage Temperature Range: -40° C ~ $+85^{\circ}$ C

Storage Condition before Soldering (Included packaging material)

Storage Temperature Range: $+5 \sim +40 \,^{\circ}$ C Humidity: 30 to 70% relative humidity


Typical Electrical Chart







LAND PATTERN





RELIABILITY TEST

Test item	Test condition / Test method	Specification
Solderability	*Solder bath temperature: 235 ± 5°C	At least 95% of a surface of each terminal
JIS C 0050-4.6	*Immersion time : 2 ± 0.5 sec	electrode must be covered by fresh solder.
JESD22-B102D	Solder : Sn3Ag0.5Cu for lead-free	
Resistance to soldering heat	*Preheating temperature : 120~150℃,	No mechanical damage.
JIS C 0050-5.4	1 minute.	Electrical specification shall satisfy the
	*Solder temperature : 270±5°C	descriptions in electrical characteristics under
	*Immersion time: 10±1 sec	the operational temperature range within -40 ~ 85°C.
	Solder : Sn3Ag0.5Cu for lead-free	Loss of metallization on the edges of each
	Measurement to be made after keeping at	electrode shall not exceed 25%.
	room temperature for 24±2 hrs	
Drop Test JIS C 0044	*Height: 75 cm	No mechanical damage.
Customer's specification.	*Test Surface: Rigid surface of concrete or steel.	Electrical specification shall satisfy the descriptions in electrical characteristics under
	*Times: 6 surfaces for each units; 2 times for each side.	the operational temperature range within -40 ~ 85°C.
Vibration	*Frequency: 10Hz~55Hz~10Hz(1min)	No mechanical damage.
JIS C 0040	*Total amplitude:1.5mm	Electrical specification shall satisfy the
	*Test times : 6hrs.(Two hrs each in three mutually perpendicular directions)	descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Adhesive Strength	*Pressurizing force :	No remarkable damage or removal of the
of Termination JIS C 0051- 7.4.3	5N (LGA terminal series) ; 5N(≦0603) ; 10N(>0603)	termination.
	*Test time: 10±1 sec	
Bending test	The middle part of substrate shall be	No mechanical damage.
JIS C 0051- 7.4.1	pressurized by means of the pressurizing rod	Electrical specification shall satisfy the
	at a rate of about 1 mm/s per second until the	descriptions in electrical characteristics under
	deflection becomes 1mm/s and then pressure	the operational temperature range within -40
	shall be maintained for 5±1 sec.	~ 85°C.
	Measurement to be made after keeping at	
	room temperature for 24±2 hours	

Approvarance			
Temperature cycle	1. 30±3 minutes at -40°C±3°C,	No mechanical damage.	
JIS C 0025	2. 10~15 minutes at room temperature,	Electrical specification shall satisfy the	
	3. 30±3 minutes at +85°C±3°C,	descriptions in electrical characteristics under the operational temperature range	
	4. 10~15 minutes at room temperature,	within -40 ~ 85°C.	
	Total 100 continuous cycles		
	Measurement to be made after keeping at		
	room temperature for 24±2 hrs		
High temperature	*Temperature: 85°C±2°C	No mechanical damage.	
JIS C 0021	*Test duration: 1000+24/-0 hours	Electrical specification shall satisfy the	
	Measurement to be made after keeping at	descriptions in electrical characteristics under	
	room temperature for 24±2 hrs	the operational temperature range within -40 ~ 85°C.	
Humidity	*Humidity: 90% to 95% R.H.	No mechanical damage.	
(steady conditions)	*Temperature : 40±2°C	Electrical specification shall satisfy the	
JIS C 0022	*Time: 1000+24/-0 hrs.	descriptions in electrical characteristics unde the operational temperature range within -40	
	Measurement to be made after keeping at	~ 85°C.	
	room temperature for 24±2 hrs		
	1000hrs data		
Low temperature	*Temperature : -40°C±2°C	No mechanical damage.	
JIS C 0020	*Test duration: 1000+24/-0 hours	Electrical specification shall satisfy the	
	Measurement to be made after keeping at	descriptions in electrical characteristics under	
	room temperature for 24±2 hrs	the operational temperature range within -40	
		~ 85°C.	



SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,

This product could sustain by reflow process three times, and the temperature below 260 $^{\circ}\!\!$ C.





Fig 2. Infrared soldering profile

ORDERING CODE

RF	CPL	160807	0	Р	3	Т
Walsin	Product	Dimension code	Unit of	Application	Code from	Packing
RF	Code	Per 2 digits of Length,	dimension	P: GSM850/ GSM 900/	Design Code	T: Taping
device	Coupler	Width, Thickness:	0 : 0.1 mm	DCS 1800 / PCS 1900		
		e.g. :	1 : 1.0 mm	Quad		
		160807 =		Band+UMTS/WCDMA		
		Length 16,		2100MHz		
		Width 08,				
		Thickness 07				

Minimum Ordering Quantity: 4000 pcs per reel.

PACKAGING




Paper Tape specifications (unit :mm)

the rape openioane (and initi)						
Index	Ao	Во	ΦD	Т	W	
Dimension (mm)	0.975 ± 0.10	1.76 ± 0.10	1.55 ± 0.05	0.75 ± 0.10	8.00 ± 0.10	
Index	E	F	Po	P1	P2	
Dimension (mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	



Reel dimensions



Index	Α	В	С	
Dimension (mm)	Ф178.0	Ф60.0	Ф13.0	

Taping Quantity:4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.

■ Temperature : +5 to +40°C

Humidity : 30 to 70% relative humidity

- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.