

Description

The UMW UCC27517DBVR device is a low voltage power MOSFET and IGBT in phase gate driver. Proprietary latch-immune of CMOS technology enables single-chip integrated architectures with high robustness. The UMW UCC27517DBVR logic input level is compatible with CMOS or TTL logic output levels down to 3.3V. The output driver has Internal Undervoltage Lockout (UVLO) circuitry with hysteresis and buffer stage of output current . The UCC27517DBVR is designed to operate over a wide VCC range of 5 V to 25 V and wide temperature range of –40°C to 125°C.


Applications

- Switch-Mode Power Supplies
- General Gate Driver
- Driving MOSFETs and IGBTs

Features


- Dual Input Design (Choice of an Inverting (IN- pin) or Non-inverting (IN+ pin) Driver Configuration)
 Unused Input Pin Can Be Used for Enable or Disable Function
- TTL and CMOS Compatible Input-Logic Threshold
- 5 to 25-V Single-Supply Range
- Operating Temperature Range of -40 to 125°C
- Undervoltage Lockout
 - -- Undervoltage Lockout turn-on threshold 4.0V -- Undervoltage Lockout turn-off threshold 3.9V
- Turn on/Turn off Delays:
 - -- Ton/Toff =30ns/30ns
- 4-A Peak Source and Sink-Drive Current

Pin Configuration





Pin Configuration and Functions



5-Pin SOT23-5 Package Top View

Pin Functions

PIN	NAME	DESCRIPTION
1	VDD	Bias supply input
2	GND	Ground: All signals are referenced to this pin.
3	IN+	Non-inverting Input: When the driver is used in inverting configuration, connect IN+ to VDD in order to enable output, OUT held LOW if IN+ is unbiased or floating.
4	IN-	Inverting Input: When the driver is used in non- inverting configuration, connect IN- to GND in order to enable output, OUT held LOW if IN- is unbiased or floating.
5	OUT	Sourcing/Sinking Current Output of Driver



Absolute Maximum Ratings

Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. All voltages are with respect to GND unless otherwise noted, Currents are positive into, negative out of the specified terminal, environment temperature is 25 $^{\circ}$ C.

Symbol	Definition	MIN	МАХ	UNIT
V _{cc}	Supply voltage range	-0.3	25	
Vo	OUT voltage range	-0.3	Vcc+0.3	V
V _{IN}	IN+, IN- voltage	-0.3	V _{CC} +0.3	
R _{thJA}	thermal resistance	_	151	°C/W
Ts	Storage temperature	-55	+150	
TJ	Operating junction temperature	—	+150	°C
TL	Lead temperature	—	300	
V _{cc}	Supply voltage range	5.0	20	
Vo	OUT voltage range	0	Vcc	V
V _{IN}	IN+, IN- voltage	0	V _{cc}	
T _A	ambient temperature	-40	125	°C



Electrical Characteristics

TA= 25°C, VCC=15V, CL=1nF(unless otherwise noted)

Symbol	Definition	MIN	ТҮР	MAX	UNIT
V _{IH}	Input signal high threshold	2.7	_	_	V
VIL	Input signal low threshold	—	—	0.8	V
V _{CCUV+}	Undervoltage Lockout (UVLO) turn-on threshold VCC	—	4.0	—	V
V _{CCUV-}	Undervoltage Lockout (UVLO) turn-off threshold VCC	—	3.9	—	V
VCCUVHY	UVLO threshold hysteresis VCC	—	0.1	—	V
I _{IN+}	Input current(IN+/IN-=HIGH)	—	50	100	μA
I _{IN-}	Input current(IN+/IN-= LOW)	—	—	5	μA
V _{OH}	High output voltage	—	—	0.35	V
V _{OL}	Low output voltage	—	_	0.35	V
lq	VCC quiescent supply current	—	180	400	μA
I _{O+}	Output high short-circuit pulse current	—	4	_	А
lo-	Output low short-circuit pulse current	—	4	_	А
t _R	Rise time	—	10	15	ns
t⊧	Fall time	_	10	15	ns
ton	Turn-on propagation delay	_	30	60	ns
t _{OFF}	Turn-off propagation delay	_	30	60	ns




Figure 1 Input-Output waveform(non-inverting)




Figure 2 Input-Output waveform(inverting)

V[®]®®®&

UMV



Typical Characteristics




Figure 3. Start-Up Current vs Temperature




Figure 5. Supply Current vs Temperature (Outputs In DC On/Off Condition)




Figure 7. Input Threshold vs Temperature




Figure 4. Operating Supply Current vs Temperature (Outputs Switching)





Figure 6. UVLO Threshold vs Temperature







Typical Characteristics(continued)




Figure 9. Output Pull-down Resistance vs Temperature




Figure 11. Fall Time vs Temperature




Figure 13. Operating Supply Current vs Frequency




Figure 10. Rise Time vs Temperature




Figure 12. Input to Output Propagation Delay vs Temperature




Figure 14. Propagation Delays vs Supply Voltage



Typical Characteristics(continued)




Figure 15. Rise Time vs Supply Voltage





Figure 16. Fall Time vs Supply Voltage



Functional Block Diagram





Device Functional Modes

Table 1 Device Logic Table				
IN+	IN-	OUT		
L	L	L		
L	Н	L		
Н	L	Н		
Н	Н	L		
L	L	L		
x ⁽¹⁾	Any	L		
Any	x ⁽¹⁾	L		

(1) Floating condition.

Typical Application





Figure 17 Non-inverting Typical Application Diagram of UCC27517DBVR






UNW®®®®®

4A Single-Channel, Low-Side, Non-Inverting Gate Driver

SOT23-5



	Dime	nsions	Dimensions		
Symbol	In Millimeters		In Inches		
	Min	Max	Min	Max	
A	1.040	1.350	0.042	0.055	
A1	0.040	0.150	0.002	0.006	
A2	1.000	1.200	0.041	0.049	
b	0.380	0.480	0.015	0.020	
с	0.110	0.210	0.004	0.009	
D	2.720	3.120	0.111	0.127	
Е	1.400	1.800	0.057	0.073	
E1	2.600	3.000	0.106	0.122	
е	0.950 typ.		0.037 typ.		
e1	1.900 typ.		0.078 typ.		
L	0.700 ref.		0.028 ref.		
L1	0.300	0.600	0.012	0.024	
θ	0 °	8°	0°	8°	

Marking



Ordering information

Order code	Package	Baseqty	Deliverymode
UMW UCC27517DBVR	SOT23-5	3000	Tape and reel