



## 1. Features

- SGT MOSFET technology
- Proprietary Advance Trench Technology
- $R_{DS(ON)}=9.0m\Omega(\text{typ.})@V_{GS}=10V$
- Low Gate Charge Minimize Switching Loss
- Fast Recovery Body Diode

## 2. Applications

- DC-DC Converters
- Ideal for high-frequency switching and synchronous rectification

## 3. Pin configuration



Pin	Function
1	Gate
2	Drain
3	Source

## 4. Ordering Information

Part Number	Package	Brand
KCB2920A	TO-263	KIA
KCP2920A	TO-220	KIA
KCM2920A	TO-247	KIA

## 5. Absolute maximum ratings

(T<sub>C</sub>= 25 °C , unless otherwise specified)

Parameter	Symbol	Ratings	Unit	
Drain-to-Source Voltage <sup>1)</sup>	V <sub>DSS</sub>	200	V	
Gate-to-Source Voltage	V <sub>GSS</sub>	±20	V	
Continuous Drain Current	T <sub>C</sub> =25 °C	I <sub>D</sub>	130	A
	T <sub>C</sub> =100 °C	I <sub>D</sub>	75	A
Pulsed Drain Current at V <sub>GS</sub> =10V <sup>2)</sup>	I <sub>DM</sub>	440	A	
Single Pulse Avalanche Energy L=10mH	EAS	2000	mJ	
Peak Diode Recovery dv/dt	dv/dt	5.0	V/ns	
Power Dissipation	P <sub>D</sub>	278	W	
Derating Factor above 25°C	P <sub>D</sub>	2.22	W/°C	
Maximum Temperature for Soldering Leads at 0.063in (1.6mm) from Case for 10 seconds, Package Body for 10 seconds	T <sub>L</sub> T <sub>PAK</sub>	300 260	°C	
Operating and Storage Temperature Range	T <sub>J</sub> &T <sub>STG</sub>	-55 to 150	°C	

Caution: Stresses greater than those listed in the “Absolute Maximum Ratings” may cause permanent damage to the device.

## 6. Thermal characteristics

Parameter	Symbol	Ratings		Unit
		TO-263,TO-220	TO-247	
Thermal Resistance, Junction-to-Case	R <sub>θJC</sub>	0.45	0.45	°C/W
Thermal Resistance, Junction-to-Ambient	R <sub>θJA</sub>	62	50	°C/W

## 7. Electrical characteristics


(T<sub>J</sub>=25°C, unless otherwise specified)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Drain-to-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250uA	200	-	-	V
Drain-to-Source Leakage Current	I <sub>DSS</sub>	V <sub>DS</sub> =200V, V <sub>GS</sub> =0V	-	-	1	uA
		V <sub>DS</sub> =160V, T <sub>J</sub> =125°C	-	-	100	uA
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	-	-	±100	nA
Drain-to-Source ON Resistance <sup>3)</sup>	R <sub>DS(ON)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =35A	-	9.0	10.5	mΩ
Gate Threshold Voltage	V <sub>GS(TH)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250uA	2.5	-	4.5	V
Input Capacitance	C <sub>iss</sub>	V <sub>GS</sub> =0V, V <sub>DS</sub> =100V, f=1.0MHZ	-	10686	-	pF
Reverse Transfer Capacitance	C <sub>rss</sub>		-	18	-	
Output Capacitance	C <sub>oss</sub>		-	392	-	
Total Gate Charge	Q <sub>g</sub>	V <sub>DD</sub> =100V, I <sub>D</sub> =55A, V <sub>GS</sub> =10V	-	143	-	nC
Gate-to-Source Charge	Q <sub>gs</sub>		-	46	-	
Gate-to-Drain (Miller) Charge	Q <sub>gd</sub>		-	25	-	
Turn-on Delay Time	t <sub>d(ON)</sub>	V <sub>DD</sub> =100V, I <sub>D</sub> =55A, R <sub>G</sub> =4.7Ω, V <sub>GS</sub> = 10V	-	45	-	nS
Rise Time	t <sub>rise</sub>		-	20	-	
Turn-Off Delay Time	t <sub>d(OFF)</sub>		-	86	-	
Fall Time	t <sub>fall</sub>		-	16	-	
Continuous Source Current	I <sub>SD</sub>	Integral PN-diode in MOSFET	-	-	110	A
Pulsed Source Current	I <sub>SM</sub>		-	-	440	A
Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =70A, V <sub>GS</sub> =0V	-	-	1.2	V
Reverse recovery time	t <sub>rr</sub>	V <sub>GS</sub> =0V, I <sub>F</sub> =55A, diF/dt=100A/μs	-	185	-	ns
Reverse recovery charge	Q <sub>rr</sub>		-	469	-	uC


Note:

- 1) T<sub>J</sub>=+25°C to +150°C
- 2) Repetitive rating; pulse width limited by maximum junction temperature.
- 3) Pulse width ≤ 380μs; duty cycle ≤ 2%.


**8. Test circuits and waveforms**




**Figure 1: On-Region Characteristics**




**Figure 2: Transfer Characteristics**




**Figure 3: On-Resistance vs. Drain Current and Gate Voltage**




**Figure 4: On-Resistance vs. Junction Temperature**




**Figure 5: On-Resistance vs. Gate-Source Voltage**




**Figure 6: Body-Diode Characteristics**



**Figure 7: Gate-Charge Characteristics**



**Figure 8: Capacitance Characteristics**



**Figure 9: Maximum Forward Biased Safe Operating Area**

**9. Test Circuits and Waveforms**




Fig. 1.1 Peak Diode Recovery dv/dt Test Circuit




Fig. 1.2 Peak Diode Recovery dv/dt Waveforms




Fig. 2.1 Switching Test Circuit




Fig. 2.2 Switching Waveforms




Fig. 3. 1 Gate Charge Test Circuit




Fig. 3. 2 Gate Charge Waveform




Fig. 4.1 Unclamped Inductive Switching Test Circuit




Fig. 4.2 Unclamped Inductive Switching Waveforms