

## 广东科尼盛电子科技有限公司 KNSCHAELECTRONICS CO., LIMITED . ==



# 规格承认书

**Specification for approval** 

客户名称:

(Customer Name)

产品名称: 铝电解电容

(Product Name) Aluminum Electrolytic Capacitor

03EC2258

客户料号:

(Customer part number)

科尼盛料号:

(KNSCHA number)

型号规格:

SHC 330UF/250V Ф16\*40L

(Specifications)

制造						
	(Manufacture) Approval					
拟制	审核	核准				
(Fiction)	(Chief)	(Approval)				
* 工程课》						
刘淑芬	刘军军	徐贵南				

客户				
	(Customer)			
	Approval			
检 验	审 核	核准		
(Inspect)	(Chief)	(Approval)		

### 广东科尼盛电子科技有限公司

KNSCHA ELECTRONICS CO., LIMITED.

No. 8th floor, A3 building, R&D center (Phase I),

Songshan Lake Intelligent Valley, Liaobu Town, Dongguan City.

TEL:0769-83698067 81035570 FAX: 0769-83861559

Email: sales@knscha.com Website: http://www.knscha.com



#### **Aluminum Electrolytic Capacitors**


Item Name	Rating	Case size	KNSCHA Lifetime
03EC2258	SHC250V330 μ F	Ф16 <b>*4</b> 0L	2000 hours

#### 1. Operating Temp. Range

#### 2. Electrical Characteristics


【Table 1】						
Rated Voltage VDC	Surge Voltage VDC	Nominal Static Capacitance (μF)		Dissipation Factor (tan δ)max 20°C 120Hz	Leakage Current 2min. 20°C ( μ A)max	Permissible Ripple Current (mArms)max 105°C120Hz
250	300	330	-20 <b>~</b> +20	0.14	1680	1900

#### 3. Dimensions



#### 4. Marking

Following items are printed with white color on black color sleeve



- 1 Rated voltage & Nominal Capacitance
- 2 Polarity (negative)
- 3 Trade Mark
- (M) Symbol of Capacitance Tolerance
- 5 Max Operating Temp.

#### **5.MULTIPLIER FOR RIPPLE CURRENT**

1. Frequency Coefficient

Trequency Obernicient					
Freq.(Hz) Cap( $\mu$ F)	60 (50)	120	300	1K	10K
0.1-47	0.75	1.00	1.35	1.55	2.00
68-680	0.80	1.00	1.25	1.34	1.50
1000-22000	0.85	1.00	1.10	1.13	1.15

2. Temperature Coefficient

•	Temperature openiolent					
	Ambient	40	60	70	05	105
	Temperature(°C)	40	60	70	85	105
	Coefficient	2.40	2.10	1.78	1.65	1.00

#### 6. Characteristics


No.	Item	Pe	rformance		Test Method	
1	Leakage Current	I= Max Leakage Current			Protection Resistor : $1000\pm10\Omega$ Applied Volt : Rated Voltage Mesauring time : $2$ minutes	
2	Static Capacitance	376 $\sim$ 564 $\mu$ F			Measured Frequency : 120Hz±20%  Measured Voltage  ≤ 0.5Vrms, 1.5 ~ 2.0VDC	
3	Dissiption Factor (tanδ)	0.14 and Und	der		Same as condition of Capacitors	
4	High Temp. Load Charac- teristics	Cap. Change	e $\leq \pm 20\%$ of initial value Factor $\leq 200\%$ of value specified in Table		Test Temp.: 105±2°C Applied voltage: Rated voltage Test Time :2,000 hours +72, -0 hours	
5	High Temp. no load Charac- teristics	Cap. Change	≦the value spe ≦±20% of initia ≦200% of value No remarkable	al value specified in Table	Test Temp.: 105±2°C No voltage applied Test Time:1000 hours +24, -0 hurs	
6	Terminal Strength	Tensile Strength Bending Strength	45N {4.5kg 25N {2.5kg		Keeping time Tensile 1∼5sec Bending 30±5sec	
7	Impedance Ratio	W V Z-25°C/Z Z-40°C/Z	+20°C	250 8 -		
8	Temperature Charac – teristics	Stage     Item     Performance       2,3     Impedance Ratio     less than the value mention       5     Cap, Change     ≤±25% against value in standard reaches temperature stability, measure performance		tage 4 2 -25±3; 3 -25±3; 4 20±2 stage 5 105±2		
9	Surge Voltage	Item       Perforemance         Leakage Current       ≤ the initial specified val         Cap, Change       ≤ ±15% against value be         Dissipation Factor       ≤ the initial specified val         Appearance       No remakable abnormality         Test Temp. 15~35°C       Test volt. Surge Volt.         Voltage apply. 1,000times of chage for 30±5sec, unand discharge for 5min30sec.			efore test ue ty Specified in 2	

#### 6-2. Characteristics

No.	Item	Performance	Test Method
10	Vibration Resistance	Capacitance Stability required Cap. Change ≤±5% of the initial specifi Appearance No remarkable abnormali Frequency: 10∼55Hz/1min. Width of vibrat Y and Z directions, each for 2 hours (Total	ty tion, 1.5mm Direction and duration X,
11	Solderbility	3/4 area of surrounding directions of surface should be covered with new solder.	Solder: Sn-Ag, Sn-Cu Type Soldering Temp: 240±5°C Dipping degree: 2~2.5mm Flux: Ethanol solution (JIS K8101) or Isopropylalchol (JIS K8839) solution of Rosin (JIS K5902)
12	Resistance to Soldering	Leakage Current       ≦ Initial specified value         Cap. Change       ≦ ± 10% of initial value         Dissipation Factor       ≦ Initial specified in value         Appearance       No remarkable abnormality	Soldering Temp. 260±5°C Soldering Time . 3~5sec. Printed wiring board:≥1.6mm
13	Resistance to Humidity	Leakage Current       ≦ Initial specified value         Cap. Change       ≦ ± 15% of initial value         Dissipation Factor       ≦ Initial spesified value         Appearance       No remarkable abnormality	Test Temp. : $40\pm2^{\circ}$ C Humidity $90\sim95\%$ Test Time : $500\pm8$ hours After the above condition,restored to normal temp, and then measured.
14	Perssure valve moment charact— erstics	There must not be thing ignition, scattering the resolution that that case works safely	Dcmethod: impress the reverse voltage and of 1A, I cancel an electric current.

#### 7 Packing method

5-1 Packaging shape, size, quantity



Component	Quanity
size	per
16*40	1200pcs.

#### 8 Related Standards JIS C 5141

#### 9 Marking on packing box

- 1 Item name
- 2 Series name
- 3 Rated Voltage
- 4 Nominal Static Capacitance
- 5 Case size
- 6 Lot No.
- 7 Quantity

#### 10 Soldeing

8-1 Soldering by soldering iron

Temperature of iron top: 270~350°C

Operating time: within 3 sec.

8-2 Flow soldering.

Preheat: PCB surface temperature 120°C±5°C

Solder Temp : 260°C±5°C Solder Dipping Temp. : 2~4sec.

#### 11 Cleaning of PC boad after soldering

Using follwing solvents is possible but make sure following condition Solvent

IPA or Alcoholic agent like Pinealpha ST-100S, Cleanthrough 750H, 750L, 710M, 750K, or Technocare FRW-14∼17

- ① Cleaning should be made by ultrasonic within 5min, at the temperature less then 60°C.
- ② Control of pollution is necessary (conductivity,pH, specific gravity, water volume)
- 3 Please do not keep near cleaning agent. Please do not store in air-tight container. Please let it dry by hot air at the temperature less than maximum operating temp.

#### 12 The situation of using

Please do not use a condenser in the next use environment.

- 1 One circumference environment(weatherability) condition.
- (a) Direct water, salt water and environment oil works or become a dew condensation state.
- (b) Environment full of harmful gas (a hydrogen chloride, sulfurous acid. nitrous acid hydrochloric acid, ammonia).
- (c) Ozone, infrared rays and the environment where radioactive rays are done collation of
- ② Vibration shock condition is extreme environment more than rule ranges of delivery specifications.

#### 13 A country of origin


A country of origin of an SHC series alminum electrolysis condenser of specifications: China

#### 14 Effective life for storage

Storage conditions:

- (1) Temperature range must be between 5-35°C
- 2 Relative humidity must be less than 75%
- 3 Must be stored indoor
- 4 Must be free from water, oil or salt water
- ⑤ Must be free from toxic gasses (hydrogen sulfide, sulfurous acid, chlorine, ammonium, etc.)
- 6 Must be free from ozone, ultraviolet rays or any other radiation
- (7) Must be kept in capacitor original package
- I Storage life is 12 months for capacitor of rated voltage  $\leq$  160V
- II Storage life is 6 months for capacitor of rated voltage  $\geq$  200V

# Aluminum Electrolytic Capacitor SHC Series Structure



No.	Name	Material
1	Case	Aluminum
	Element (Electrode)	High Purity Aluminum foil
2	(Separator)	Manila hemp pulp
	(Electrolyte)	
3	Rubber Bung	Synthetic Rubber
4	Sleeve	PVC
<b>⑤</b>	Lead Wire	Tin plated Steel Wire

Controls of ozone layer destructive chemical materials

Regulated materials: CFCs, Halon, Carbon Tetrachloride, 1.1.1-Trichloroethane The products and parts do not include the above materials

The products and parts are not used the above materials on process.

The products and parts are not used PBBOs (Poly Bromo Bi-phenyl Oxides ).

All materials are mentioned as existing chemical material in the "Law of examine and control of Production of Chemical Material"

The products are not listed in Appendix 1 of Export Trade Rule and Regulation

A condenser of this series supports RoHS regulation.