

● General Description

The AGM60P90D combines advanced trench MOSFET technology with a low resistance package to provide extremely low $R_{DS(ON)}$. This device is ideal for load switch and battery protection applications.

● Features

- Advance high cell density Trench technology
- Low $R_{DS(ON)}$ to minimize conductive loss
- Low Gate Charge for fast switching
- Low Thermal resistance


● Application

- MB/VGA Vcore
- SMPS 2nd Synchronous Rectifier
- POL application
- BLDC Motor driver

Product Summary

BVDSS	RDS _{ON}	ID
-60V	8.2mΩ	-90A

TO-252 Pin Configuration



Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
AGM60P90D	AGM60P90D	TO-252	330mm	16mm	2500

Table 1. Absolute Maximum Ratings (TA=25°C)

Symbol	Parameter	Value	Unit
VDS	Drain-Source Voltage (VGS=0V)	-60	V
VGS	Gate-Source Voltage (VDS=0V)	±20	V
ID	Drain Current-Continuous(Tc=25°C) (Note 1)	-90	A
	Drain Current-Continuous(Tc=100°C)	-62	A
IDM (pulse)	Drain Current-Continuous@ Current-Pulsed (Note 2)	-360	A
PD	Maximum Power Dissipation(Tc=25°C)	105	W
	Maximum Power Dissipation(Tc=100°C)	42	W
EAS	Avalanche energy (Note 3)	320	mJ
TJ,TSTG	Operating Junction and Storage Temperature Range	-55 To 150	°C

Table 2. Thermal Characteristic

Symbol	Parameter	Typ	Max	Unit
R _{θJA}	Thermal Resistance Junction-ambient (Steady State) ¹	---	120	°C/W
R _{θJC}	Thermal Resistance Junction-Case ¹	---	1.2	°C/W

Table 3. Electrical Characteristics (TJ=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BVDSS	Drain-Source Breakdown Voltage	VGS=0V ID=-250μA	-60	--	--	V
IDSS	Zero Gate Voltage Drain Current	VDS=-60V, VGS=0V	--	--	-1	μA
IGSS	Gate-Body Leakage Current	VGS=±20V, VDS=0V	--	--	±100	nA
VGS(th)	Gate Threshold Voltage	VDS=VGS, ID=-250μA	-1.0	-1.8	-2.5	V
gFS	Forward Transconductance	VDS=5V, ID=-5A	--	25	--	S
RDS(on)	Drain-Source On-State Resistance	VGS=-10V, ID=-20A	--	8.2	12	mΩ
		VGS=-4.5V, ID=-15A	--	10	15	mΩ
Dynamic Characteristics						
Ciss	Input Capacitance	VDS=-30V, VGS=0V, F=1MHZ	--	6550	--	pF
Coss	Output Capacitance		--	475	--	pF
Crss	Reverse Transfer Capacitance		--	328	--	pF
Rg	Gate resistance	f=1.0MHz	--	--	--	Ω
Switching Times						
td(on)	Turn-on Delay Time	VGS=-10V, VDS=-30V, ID=-12A, RGEN=2.5Ω	--	10	--	nS
tr	Turn-on Rise Time		--	60	--	nS
td(off)	Turn-Off Delay Time		--	99	--	nS
tf	Turn-Off Fall Time		--	258	--	nS
Qg	Total Gate Charge	VGS=-10V, VDS=-15V, ID=-12A	--	138	--	nC
Qgs	Gate-Source Charge		--	67	--	nC
Qgd	Gate-Drain Charge		--	132	--	nC
Source-Drain Diode Characteristics						
ISD	Source-Drain Current(Body Diode)		--	--	-90	A
VSD	Forward on Voltage	VGS=0V, IS=-10A	--	--	-1.2	V
trr	Reverse Recovery Time	Isd=-10A, dI/dt=100A/μs, TJ=25°C	--	--	--	ns
Qrr	Reverse Recovery Charge		--	--	--	nc

Notes 1.The maximum current rating is package limited.

Notes 2.Repetitive Rating: Pulse width limited by maximum junction temperature

Notes 3.EAS condition: TJ=25°C

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. Typical $-V_{GS(TH)}$ Gate-Source Voltage Vs. T_j




Fig3. Typical Transfer Characteristics




Fig4. Typical Normalized On-Resistance Vs. T_j




Fig5. Typical On Resistance Vs Gate-Source Voltage




Fig6. Typical On Resistance Vs Drain Current and Gate

Typical Characteristics




Fig7. Typical Source-Drain Diode Forward Voltage




Fig8. Maximum Safe Operating Area




Fig9. Typical Capacitance Vs. Drain-Source Voltage




Fig10. Typical Gate Charge Vs. Gate-Source Voltage




Fig11. Power Dissipation Vs. Case Temperature




Fig12. Maximum Drain Current Vs. Case Temperature

Typical Characteristics




Fig13 . Normalized Maximum Transient Thermal Impedance





Fig14. Unclamped Inductive Test Circuit and waveforms









Fig15. Switching Time Test Circuit and waveforms

TO-252 Package Outline Data



SYMBOL	MILLIMETER		
	MIN	Typ.	MAX
A	2.200	2.300	2.400
A1	0.000		0.127
b	0.640	0.690	0.740
c (电镀后)	0.460	0.520	0.580
D	6.500	6.600	6.700
D1	5.334 REF		
D2	4.826 REF		
D3	3.166 REF		
E	6.000	6.100	6.200
e	2.286 TYP		
h	0.000	0.100	0.200
L	9.900	10.100	10.300
L1	2.888 REF		
L2	1.400	1.550	1.700
L3	1.600 REF		
L4	0.600	0.800	1.000
ϕ	1.100	1.200	1.300
θ	0°		8°
θ_1	9° TYP		
θ_2	9° TYP		

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	7.050	7.100	7.150
A1	0.960	1.010	1.060
A2	2.250	2.300	2.350
A3	0.000	0.050	0.100
b	0.760REF.		
b1	1.000REF.		
c	0.508REF.		
c1	0.508REF.		
D	6.550	6.600	6.650
D1	5.220	5.320	5.420
E	0.950	1.000	1.050
E1	9.700	9.900	10.100
E2	6.050	6.100	6.150
e	2.286BSC		
e1	4.572REF.		
L	2.650	2.800	2.950
L1	0.700	0.800	0.900
θ_1	7° REF.		
R	1.300REF.		
R1	0.250REF.		

Disclaimer:

The information provided in this document is believed to be accurate and reliable. however, Shenzhen Core Control Electronics Technology Co., Ltd. does not assume any responsibility for the following consequences. Do not consider the use of such information or use beyond its scope.

The information mentioned in this document may be changed at any time without notice.

The products and information provided in this document do not infringe patents. Shenzhen Core Control Electronics Technology Co., Ltd. assumes no responsibility for any infringement of any other rights of third parties. The result of using such products and information.

This document is the second version issued on May 10th, 2023. This document replaces all previously provided information.

 It is a registered trademark of Shenzhen Core Control Electronics Technology Co., Ltd.

Copyright © 2017 Shenzhen Core Control Electronics Technology Co., Ltd. all rights reserved.