

# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25

### SPECIFICATIONS

1. Current rating: 2A AC, DC
  2. Voltage rating: 250V AC, DC
  3. Temperature range: -40°C ~ +105°C
  4. Insulation resistance: 1000MΩ Min.
  5. Withstanding voltage: 500V AC/ minute.
  6. Contact resistance: 20mΩ Max.
- Max. Processing Temp: 240°C~260°C for 30-60 seconds  
(260°C for 10 seconds)

### Material:





Insulator: PA6T UL 94V-0 Black  
Contact: Brass/Matte-tin plated Gold-Flash  
Mate with PM200 /I200 series

### Ordering Code:

BH200R-xxP

- 1 2  
1. 序列号  
2. Pin位数: 10P=2x05P

No. of Pins/Row	Dimension	
	A	B
06	10.0	19.5
08	14.0	23.5
10	18.0	27.5
12	22.0	31.5
14	26.0	35.5
16	30.0	39.5
18	34.0	43.5
20	38.0	47.5
24	46.0	55.5
26	50.0	59.5
30	58.0	67.5
34	66.0	75.5
40	78.0	87.5
50	98.0	107.5
68	134.0	143.5



X.±0.50	X.°±	PART NO: BH200R-xxP	<b>XFCN 兴飞连接器</b>		
.XX±0.25	.X°±				
.XX±0.15	.XX°±	TITLE: 2.00mm 简易牛角 双排 DIP 90°	0769-82001899		
.XXX±0.10	.XXX°±		www.xfconn.com		
UNITS:	mm		DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD		VIEW	
		CHKD		SCALE	SHEET
		DRAW	Wang	NONE	REV
		DATE	2024.01.20	1:1	A1