




REV.	DESCRIPTION OF REVISIONS	APPR.	CHEC.	DRAW.	DATE
△	NEW			Zoey	2021/04/27
△	Original Model M6703-1			Jicks	2023/10/19



- 备注:
1. 材质:
胶芯: PBT, UL 94V-0, 黑色
端子: 黄铜 C2680R-H
接地片: 不锈钢 SUS304R-H
 2. 电镀:
所有区域镀镍底40u"最小
焊接区域: 镀亮锡80~150u"
 3. 插入力: 39.2N最大
 4. 拔出力: 6.67N最小
 5. 额定电流: 0.5A
 6. 接触阻抗: 40毫欧最大
 7. 耐电压: 500V交流电
 8. 绝缘阻抗: 1000MΩ最小

RECOMMENDED P.C.B LAYOUT
COMPONENT SIDE(TOLERANCE ±0.05)

Pin Type	Dim.L	Pin No
Detect	3.50mm	36.67
General	4.25mm	All other pins
Power	5.00mm	1.17.34.35.51.68

Products P/N M6703-68800016-0013

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	BASE	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	68	Copper Alloy	Contact area: G/F gold
3	FLAKE	2	SUS	Plated: Tin over all
4	PLUG	1	Hi-temp Thermoplastic	Black UL94V-0

Unless otherwise specified, other tolerance are:

®
MUP MUP INDUSTRIAL CO.,LTD.

X ±0.45	X* ±5*
X.X ±0.35	X.X* ±4*
X.XX ±0.25	X.XX* ±3*
X.XXX ±0.10	X.XXX* ±2*

NAME: **PCMCIA Connector**
MODEL NO: **MUP-M6703-01**
TYPE: **H8.0 (68Pin)**

PROJ. UNIT mm SCALE 1:1
CUSTOMER DRAWING

DRAWN Zoey 2021 04 27
CHECKED Keye 2021 04 27
APPROVAL Simon 2021 04 27

DWG NO.:
DWG-M6703-01-01
SHEET 1/1
REVISION 2

