



REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
①	NEW			HUABO	2021/6/21
②	Original Model: C7402-1			HUABO	2023/10/28



RECOMMENDED P.C.B LAYOUT  
COMPONENT SIDE(TOLERANCE ±0.05)

TECHNICAL CHARACTERISTICS

- General Characteristics  
H=1.20 mm  
Durability: 2,000 cycles min.
- Electrical Characteristics  
Contact resistance: 50mΩ typical, 100mΩ max  
Insulation resistance: >1000MΩ/500V DC
- Solderability  
IR reflow: 250°C, 5sec. Max
- Environmental Characteristics  
Operating temperature: -40°C~+85°C  
Operating humidity: 10%~+95%RH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	CONTACT	10	Copper Alloy	Contact area: 15u"Gold plated

Unless otherwise specified, other tolerance are:

X	±0.35	X'	±5'
X.X	±0.25	X.X'	±4'
X.XX	±0.15	X.XX'	±3'
X.XXX	±0.10	X.XXX'	±2'

**MUP** MUP INDUSTRIAL CO.,LTD.

NAME: **SIM Card Connector**  
MODEL NO: **MUP-C7402-01**  
TYPE: **H1.2 without post 10p**

PROJ.	UNIT	SCALE	DRAWN	HUABO 2021/6/21	DWG NO.:
①	mm	1:1	CHECKED	HUABO 2021/6/21	DWG-C7402-01-01
CUSTOMER DRAWING			APPROVAL	Wang 2021/6/21	SHEET
					1/1
					REVISION
					2

