




REV.	DESCRIPTION OF REVISIONS	APPR.	CHEC.	DRAW.	DATE
△	NEW			HUABO	2017/03/08
△	Revise shell			HUABO	2022/10/11
△	Original Model:M617-2			HUABO	2023/12/15




RECOMMENDED P.C.B LAYOUT  
COMPONENT SIDE(TOLERANCE ±0.05)



TECHNICAL CHARACTERISTICS

- General Characteristics  
Durability: 5000 cycles min.
- Electrical Characteristics  
Contact resistance: 50mΩ typical, 100mΩ max  
Insulation resistance: >1000MΩ/500V DC
- Solderability  
Vapor phase: 215°C, 30sec.Max  
IR reflow: 250°C, 5sec.Max  
Manual soldering: 370°C, 3sec.Max
- Environmental Characteristics  
Operating temperature: -40°C~+85°C  
Operating humidity: 10%~+95%RH



ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	8	Copper Alloy	Contact area:Gold plated
3	SHELL	1	Stainless Steel	Ni plated
4	DETECT 1	1	Copper Alloy	Contact area:Gold plated
5	DETECT 2	1	Copper Alloy	Contact area:Gold plated

Unless otherwise specified, other tolerance are:

**MUP** MUP INDUSTRIAL CO.,LTD.

NAME: **T-Flash Card Connector**

MODEL NO: **MUP-M6017-02**

TYPE: **H2.8 Without post 8p**

PROJ.	UNIT	SCALE	DRAWN	Zoey	Mar.08.2017	DWG NO.:	DWG-M6017-02-01
⊕	mm	1:1	CHECKED	Zoey	Mar.08.2017	SHEET	1/1
CUSTOMER DRAWING			APPROVAL	Wang	Mar.08.2017	REVISION	2