

MCMB-0518 Series

High Current Molded Power Inductors

FEATURES

- Powder iron core material
- Magnetically shielded, low EMI
- High current carrying capacity, Low core losses
- Frequency range up to 3MHz
- Operate temperature range -40° C \sim +125 $^{\circ}$ C (Including self temp. rise)
- RoHS compliant

APPLICATIONS

- Voltage Regulator Module (VRM)
- Multi-phase regulators
- Point-of-load modules
- Smart phone POL modules
- SSD modules
- Notebook regulators
- Battery power systems
- Graphics cards
- Data networking and storage systems

Explanation of Part Number

MCMB -0518 -1R0 M T

1 2 3 4 5

- ♦ 1:Product Series:Metal Alloy Molding Power Inductor
- ♦ 2:Dimensions:
- 3: Initial inductance value: 1R0 = 1.0uH
- ♦ 4:Tolerance of Inductance:M:±20%
- ♦ 5:Packing:Tape Carrier Package










Dimensions: [mm]



Series	А	В	С	D	E	I Тур.	Ј Тур.	Н Тур.
MCMB-0518	5.2±0.2	5.4±0.35	1.6±0.2	1.2±0.2	2.2±0.3	1.9	2.2	2.5

Electrical Properties:

Part Number	Inductance	DC Resistance	Saturation Current		Heat Rating Current	
	@100KHz,1V	Max.	Max.	Тур.	Max.	Тур.
Units	μH	mΩ	Α		Α	
Symbol	L	DCR	Isat		Irms	
MCMB-0518-R47MT	0.47±20%	9	9.60	12.0	9.50	10.5
MCMB-0518-R56MT	0.56±20%	10	8.80	11.0	8.20	9.50
MCMB-0518-R68MT	0.68±20%	13.8	9.30	10.5	7.70	8.70
MCMB-0518-1R0MT	1.0±20%	17	7.20	9.00	7.20	8.00
MCMB-0518-1R5MT	1.5±20%	26	6.40	8.00	6.60	7.50
MCMB-0518-2R2MT	2.2±20%	35	4.80	6.00	4.20	5.00
MCMB-0518-3R3MT	3.3±20%	58	3.84	4.80	3.80	4.50
MCMB-0518-4R7MT	4.7±20%	85	3.20	4.00	3.00	3.50
MCMB-0518-6R8MT	6.8±20%	120	2.72	3.40	2.40	2.80
MCMB-0518-100MT	10±20%	155	2.00	2.50	2.20	2.50


Notes

- %1: All test data is referenced to 20°C ambient;
- ※2: Rated current: Isat or Irms, whichever is smaller;
- ※3: Isat(Typ): DC current at which the inductance drops approximate 30% from its value without current;
- *4: Isat(Max): DC current at which the inductance drops approximate 20% from its value without current;
- %5: Irms(Typ): DC current that causes the temperature rise (\triangle T =40°C) from 20°C ambient.
- %6: Irms(Max): DC current that causes the temperature rise (\triangle T =20°C) from 20°C ambient.
- %7: Absolute maximum voltage 30VDC




TYPICAL ELECTRICAL CHARACTERISTICS







.....




MCMB-0518-2R2MT




MCMB-0518-4R7MT




MCMB-0518-R56MT




MCMB-0518-1R5MT



MCMB-0518-3R3MT




MCMB-0518-6R8MT





MCMB-0518-100MT






Reliability and Test Condition

Item	Specification and Requirement	Test Method		
item				
Solderability	The surface of terminal immersed shall	Solder heat proof:		
	be minimum of 95% covered with a new	 Preheating: 160 ± 10 °C Retention time: 245 ± 5 °C for 2 ± 0.5 seconds 		
	coating of solder			
Vibration	Inductance change: Within ± 10%	1. Vibration frequency:		
		(10 Hz to 55 Hz to 10Hz) in 60 seconds as a period		
	Without mechanical damage such as	2. Vibration time:		
	break	Period cycled for 2 hours in each of 3 mutual		
		perpendicular directions.		
		3. Amplitude: 1.5 mm max.		
		1. Peak value: 100 G		
Shock	Inductance change: Within ±10% Without	2. Duration of pulse: 11ms		
	mechanical damage such as break	3. 3 times in each positive and negative direction of 3		
		mutual perpendicular directions		
Endurance Reli	<u> </u>			
Item	Specification and Requirement	Test Method		
	Inductance change: Within ± 10% Without distinct damage in appearance	Repeat 100 cycles as follow:		
		(-55 ± 2 °C; 30 ± 3 min)		
Thermal		→(Room temp., 5 min)		
Shock		\rightarrow (+125 ± 2 °C, 30 ± 3 min)		
		→ (Room temp., 5 min)		
		2. Recovery: 48 + 4 / -0 hours of recovery under the		
		standard condition after the test.		
High	Inductance change: Within ± 10%	1. Environment condition: 85 ± 2 ℃		
Temperature	Without distinct damage in appearance	Applied Current: Rated current		
Resistance	This are are are a series of the series of t	2. Duration: 1000 + 4 / -0 hours		
		1. Environment condition: 60 ± 2 ℃		
Humidity	Inductance change: Within ± 10%	Humidity: 90–95%		
Resistance	Without distinct damage in appearance	Applied Current: Rated current		
		2. Duration: 1000 + 4 / -0 hours		
Low	Inductance change: Within ± 10%	Store temperature:		
Temperature	Without distinct damage in appearance	-55 ± 2 °C,1000 + 4 / -0 hours		
Store	Tritiout distinct damage in appearance	-55 12 C,1000 1 47 -0 Hours		
High	Inductance change: Within ± 10%	Store temperature:		
Temperature		Store temperature: +125 ± 2 ℃,1000 + 4 / -0 hours		
Store	Without distinct damage in appearance	123 12 C, 1000 147-0 Hours		




Tape Packaging Dimensions



A0	В0	K0	t
5.7 ± 0.10	5.9 ± 0.10	2.3 ± 0.15	0.35 ± 0.05

Reel Dimensions



Packing Quantity:2000pcs/Reel



Recommended Soldering Technologies

(1) Re-flowing Profile

Preheat condition: 150 ~200 °C/60~180 sec.


Allowed time above 217°C: 80~120sec.

Max temp: 260°C

Max time at max temp: 10 sec.

Solder paste: Sn/3.0Ag/0.5Cu

Allowed Reflow time: 2x max



(2) Iron Soldering Profile

Iron soldering power: Max.

30W Pre-heating: 150°C/60sec.

Soldering time: 3sec. Max.

Solder paste: Sn/3.0Ag/0.5Cu

Max.1 times for iron soldering

