



9311/DM9311 4-Line to 16-Line Decoders/Demultiplexers


General Description

Each of these 4-line-to-16-line decoders utilizes TTL circuitry to decode four binary-coded inputs into one of sixteen mutually exclusive outputs when both the strobe inputs, G1 and G2, are low. The demultiplexing function is performed by using the 4 input lines to address the output line, passing data from one of the strobe inputs with the other strobe input low. When either strobe input is high, all outputs are high. These demultiplexers are ideally suited for implementing high-performance memory decoders. All inputs are buffered and input clamping diodes are provided to minimize transmission-line effects and thereby simplify system design.

Features

- Pin for pin with popular DM54154/74154
- Decodes 4 binary-coded inputs into one of 16 mutually exclusive outputs
- Performs the demultiplexing function by distributing data from one input line to any one of 16 outputs
- Input clamping diodes simplify system design
- High fan-out, low-impedance, totem-pole outputs
- Typical propagation delay 19 ns
- Typical power dissipation 170 mW
- Alternate Military/Aerospace device (9311) is available. Contact a National Semiconductor Sales Office/Distributor for specifications.

Connection Diagram



Order Number 9311DMQB, 9311FMQB, DM9311J or DM9311N
See NS Package Number J24A, N24A or W24C

TL/F/6804-1

Absolute Maximum Ratings (Note)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

| | |
|--------------------------------------|-----------------|
| Supply Voltage | 7V |
| Input Voltage | 5.5V |
| Operating Free Air Temperature Range | |
| Military | -55°C to +125°C |
| Commercial | 0°C to +70°C |
| Storage Temperature Range | -65°C to +150°C |

Note: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Recommended Operating Conditions

| Symbol | Parameter | Military | | | Commercial | | | Units |
|-----------------|--------------------------------|----------|-----|------|------------|-----|------|-------|
| | | Min | Nom | Max | Min | Nom | Max | |
| V _{CC} | Supply Voltage | 4.5 | 5 | 5.5 | 4.75 | 5 | 5.25 | V |
| V _{IH} | High Level Input Voltage | 2 | | | 2 | | | V |
| V _{IL} | Low Level Input Voltage | | | 0.8 | | | 0.8 | V |
| I _{OH} | High Level Output Current | | | -0.8 | | | -0.8 | mA |
| I _{OL} | Low Level Output Current | | | 16 | | | 16 | mA |
| T _A | Free Air Operating Temperature | -55 | | 125 | 0 | | 70 | °C |

Electrical Characteristics over recommended operating free air temperature range (unless otherwise noted)

| Symbol | Parameter | Conditions | Min | Typ (Note 1) | Max | Units | |
|-----------------|-----------------------------------|--|-----|--------------|------|-------|----|
| V _I | Input Clamp Voltage | V _{CC} = Min, I _I = -12 mA | | | -1.5 | V | |
| V _{OH} | High Level Output Voltage | V _{CC} = Min, I _{OH} = Max V _{IL} = Max, V _{IH} = Min | 2.4 | 3.4 | | V | |
| V _{OL} | Low Level Output Voltage | V _{CC} = Min, I _{OL} = Max V _{IH} = Min, V _{IL} = Max | | 0.25 | 0.4 | V | |
| I _I | Input Current @ Max Input Voltage | V _{CC} = Max, V _I = 5.5V | | | 1 | mA | |
| I _{IH} | High Level Input Current | V _{CC} = Max, V _I = 2.4V | | | 40 | μA | |
| I _{IL} | Low Level Input Current | V _{CC} = Max, V _I = 0.4V | | | -1.6 | mA | |
| I _{OS} | Short Circuit Output Current | V _{CC} = Max (Note 2) | MIL | -20 | | -55 | mA |
| | | | COM | -18 | | -57 | |
| I _{CC} | Supply Current | V _{CC} = Max (Note 3) | MIL | | 34 | 49 | mA |
| | | | COM | | 34 | 56 | |

Note 1: All typicals are at V_{CC} = 5V, T_A = 25°C.

Note 2: Not more than one output should be shorted at a time.

Note 3: I_{CC} is measured with all inputs grounded and all outputs open.

Switching Characteristics at $V_{CC} = 5V$ and $T_A = 25^\circ C$ (See Section 1 for Test Waveforms and Output Load)


| Symbol | Parameter | From (Input) To (Output) | $R_L = 400\Omega, C_L = 15\text{ pF}$ | | Units |
|-----------|--|-----------------------------|---------------------------------------|-----|-------|
| | | | Min | Max | |
| t_{PLH} | Propagation Delay Time Low to High Level Output | Data to Output | | 27 | ns |
| t_{PHL} | Propagation Delay Time High to Low Level Output | Data to Output | | 30 | ns |
| t_{PLH} | Propagation Delay Time Low to High Level Output | Strobe to Output | | 25 | ns |
| t_{PHL} | Propagation Delay Time High to Low Level Output | Strobe to Output | | 27 | ns |

Function Table

| Inputs | | | | | Outputs | | | | | | | | | | | | | | | | | |
|--------|----|---|---|---|---------|---|---|---|---|---|---|---|---|---|---|----|----|----|----|----|----|---|
| G1 | G2 | D | C | B | A | 0 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | |
| L | L | L | L | L | L | L | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H |
| L | L | L | L | L | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H |
| L | L | L | L | H | L | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H | H | H |
| L | L | L | H | L | L | H | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H | H |
| L | L | L | H | L | H | H | H | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H |
| L | L | L | H | H | H | H | H | H | H | H | H | L | H | H | H | H | H | H | H | H | H | H |
| L | L | H | L | L | L | H | H | H | H | H | H | H | H | L | H | H | H | H | H | H | H | H |
| L | L | H | L | L | H | H | H | H | H | H | H | H | H | H | L | H | H | H | H | H | H | H |
| L | L | H | L | H | L | H | H | H | H | H | H | H | H | H | H | L | H | H | H | H | H | H |
| L | L | H | H | L | L | H | H | H | H | H | H | H | H | H | H | H | L | H | H | H | H | H |
| L | L | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H | H | L | H | H | H | H |
| L | L | H | H | H | L | H | H | H | H | H | H | H | H | H | H | H | H | H | L | H | H | H |
| L | L | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | L | H | L |
| L | H | X | X | X | X | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H |
| H | L | X | X | X | X | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H |
| H | H | X | X | X | X | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H | H |

H = High Level, L = Low Level, X = Don't Care.

Logic Diagram



TL/F/6604-2