

✓  
**54S/74S64** 011604  
 4-2-3-2-INPUT AND-OR-INVERT GATE

**ORDERING CODE:** See Section 9

<b>PKGS</b>	<b>PIN OUT</b>	<b>COMMERCIAL GRADE</b>	<b>MILITARY GRADE</b>	<b>PKG TYPE</b>
		V <sub>CC</sub> = +5.0 V ±5%, T <sub>A</sub> = 0° C to +70° C	V <sub>CC</sub> = +5.0 V ±10%, T <sub>A</sub> = -55° C to +125° C	
Plastic DIP (P)	A	74S64PC		9A
Ceramic DIP (D)	A	74S64DC	54S64DM	6A
Flatpak (F)	A	74S64FC	54S64FM	3I

**INPUT LOADING/FAN-OUT:** See Section 3 for U.L. definitions

<b>PINS</b>	54/74S (U.L.) HIGH/LOW
Inputs Outputs	1.25/1.25 25/12.5

**DC AND AC CHARACTERISTICS:** See Section 3\*

<b>SYMBOL</b>	<b>PARAMETER</b>	<b>54/74S</b>		<b>UNITS</b>	<b>CONDITIONS</b>	
		<b>Min</b>	<b>Max</b>		<b>V<sub>IN</sub> = Gnd</b>	<b>V<sub>CC</sub> = Max</b>
I <sub>CCH</sub>	Power Supply Current	12.5	16	mA	**	
I <sub>CCL</sub>						
t <sub>PLH</sub> t <sub>PHL</sub>	Propagation Delay	2.0 2.0	5.5 5.5	ns	Figs. 3-1, 3-4	

\*DC limits apply over operating temperature range; AC limits apply at T<sub>A</sub> = +25° C and V<sub>CC</sub> = +5.0 V.

\*\*I<sub>CCL</sub> is measured with all inputs of one gate open and remaining inputs grounded.

**CONNECTION DIAGRAM  
PINOUT A**

