

DTHD04-1-4P ✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTHD

TE Internal #: DTHD04-1-4P

Housing for Male Terminals, Wire-to-Wire, 1 Position, Sealable, Black, Wire & Cable, Power, Cable Mount (Free-Hanging), Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTHD Housings



Connector System: **Wire-to-Wire**

Number of Positions: 1

Connector & Housing Type: **Housing for Male Terminals**

Sealable: **Yes**

Mating Pin Diameter: 5.72 mm [.225 in]

[All DEUTSCH DTHD Housings \(14\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	1
Number of Rows	0

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V



Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 4
Contact Type	Pin
Mating Pin Diameter	5.72 mm[.225 in]
Contact Current Rating (Max)	100 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	With
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PEI (Polyetherimide)
------------------	----------------------

Dimensions

Connector Height	43.18 mm[1.7 in]
Product Width	26.54 mm[1.045 in]
Product Length	52.53 mm[2.068 in]
Compatible Insulation Diameter Range	6.63 – 10.67 mm[.261 – .42 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	Not Tested
UL Flammability Rating	Not tested

Packaging Features

Packaging Quantity	500
Packaging Method	Box



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer







This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-D48-PCH8172 DEUTSCH DTHD Housings</p>	 <p>TE Part # 0460-204-0490 PIN, SOLID, SIZE 4, 6AWG, NI</p>	 <p>TE Part # CAT-D487-M8649 DEUTSCH DT Mounting Clips</p>	 <p>TE Part # 1924487-2 MOUNTING CLIP, AMPSEAL 16</p>
--	---	---	--



Also in the Series | DEUTSCH DT



Also in the Series | DEUTSCH DTHD



Automotive Housings(22)



Other Automotive Connector Accessories(1)

Customers Also Bought



TE Part #DRC12-40PA
DEUTSCH DRC Housings



TE Part #HDP26-18-6SN
DEUTSCH HDP20 Housings



TE Part #2-2371035-1
PIN CONN CVR,3POS,DIA 4MM,CVE
BLIND PLUG



TE Part #2358664-5
FLAP, ASSY, INLET COMBO 1, LEFT,
LED



TE Part #2371494-1
DIE SET HVA630-2P 2X4MM2



TE Part #2407805-1
COVER,SHIPPING CAP FOR HD1000
PLUG



TE Part #2407666-2
BLIND PLUG BLOCK ASSAMBLY,
TOOL UNLOCK.



TE Part #400-414DA-4SPEC
SZ 4 DIE ASM

Documents

Product Drawings

[REC, 1P, BLK, N, SIZE 4](#)

English

[REC, 1P, BLK, N, SIZE 4](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_DTHD04-1-4P_99.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_DTHD04-1-4P_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DTHD04-1-4P_99.3d_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English