

т	۵	н п	m	C C







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 21

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Composite	
	-Shell Plating	: Olive drab Cadmium	
	-Insulator	: Thermoplastic	
	-Contacts	: Copper Alloy	
	-Seals & Grommet	: Silicon Elastomer	
	-Contact Plating	: Gold over copper Alloy 0.8µm minimum	
	-Durability	: 500 Mating cycles	
	-Delivered with Souriau contacts and Accessories		
	-Temperature Range	: -65°C to +175°C	
	-Salt Spray	: 2000 hours	
	-Contact Plating -Durability -Delivered with Souria -Temperature Range	: Silicon Elastomer : Gold over copper Alloy 0.8µm minimu : 500 Mating cycles u contacts and Accessories : -65°C to +175°C	

: 50.8 g ± 10%

8D 0

G

21

J

35

В

F

Ν

Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
PP	4.93±0.2			
R1	31.75			
R2	29.36			
S	39.7±0.3			
V'	18.7+1.4/-0			
W'	2.1/4.35			
Ζ'	32 Max			
VV THREAD	M31x1-6g			


ORIENTATION : N

CONTACT LAYOUT : 21-35

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for a due to a use of the Products the Specifications issued by either (professional recommend



	œ		A				
					4		
	AMPLE	tu or dom]	3		
s whic er of t	any non-conformity or damage which does not comply with r of the Parties or by a third party dation, technical notice.)						
untry FR	Jurisd	liction & Cont Not Listed	rol List		2		
1J3	J35BN						
				MOD N°			
		CUSTOME	R DRAWING				
	e Receptacle 8D series						
ar			PROJECT 59		1		
J.CC	COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
				SHEET			
13;	5BN-C B		A	1/2	J		

