

## NOTES:

- 1) CONTACT BARREL RANGE: 16AWG TO 18AWG
- 2) RECOMMENDED CRIMP TOOLS: HAND CRIMPER: MFX-3959 PNEUMATIC CRIMPER: MFX-3960
- 3) EXTRACTION TOOL: QXRT16
- 4) MATERIALS:

HOUSING BODY: ZINC DIE CAST, NICKEL PLATED INSULATION INSERT: PA66, UL94/V-0 CONTACT: BRASS, GOLD FLASH PLATED SEAL AND O-RING: NBR (NITRILE BUTADIENE RUBBER)


5) ELECTRICAL DATA:

- a) CURRENT (MAX): 13A
- b) VOLTAGE (MAX): 500V AC/DC
- c) INSULATION RESISTANCE (MIN): 5000M OHMS
- d) TEST VOLTAGE (BETWEEN CONTACTS): 3050V

- 6) TECHNICAL DATA:
  - a) TEMPERATURE RANGE: -40°C TO 105°C
  - b) PROTECTION: IP67 (MATED CONDITION)
  - c) MATING CYCLES: >500
  - d) VIBRATION RESISTANCE PER MIL-STD-202 METHOD 204
  - e) THERMAL SHOCK PER MIL-STD-202 METHOD 207
- f) 48 HOUR SALT SPRAY PER MIL-STD-202 METHOD 101
- 7) RoHS COMPLIANT

REVISI□NS											
REV	ECO	DESCRIPTION	DATE	BY	APPR						
01	1	CUSTOMER DRAWING	-	-	_						
02	_	CHANGED VOLTAGE FROM 250V TO 500V	18JAN22	MRF	DR						

ILLUSTRATION: COMPLETE KIT



19 MP16M23		F CONTACT.		ACT, F	T, PIN, SIZE 16			2
1	RT071619			NECTOR			1	
QUANTITY	PART N	IUMBER	DESCRIPTION			ITEM		
		MA	TEF	RIAI	_S LI	ST		
UNLESS OTHERWISE SPECIFIED		SIGNATURE	S DA	TE	∃ Δmnnen∩i			
	1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference =   MATERIAL SPECIFICATIONS:		10SE	P13				
2 PL DEC ±0.15								
3) Note reference				44724 Morley Drive Clinton Township, MI 48036			0026	
MATERIAL SPECIFICA					Clinton Township, Wi 46036			
			CUSTOMER:			KIT. ECO-MATE		
PROCESS OFFICIAL TIONS		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL		ES,	101, 200 W/ (12			
PROCESS SPECIFICATIONS:				OF GHTS	3 C-	RT071619	PNH-K	02
NEXT ASS'Y:	NEXT ASS'Y:		MANUFACTURING VARIATIONS.		LE:NONE		SHEET 1 OF	1

KIT, ECD-MATE

REV:02 SH