


REVISIONS ECO APPR REV DESCRIPTION DATE B2 ADD EXPLANATION FOR OPERATIOIN MAY-5-2015 ARROW TOMMY UPDATE RATED VOLTAGE ВЗ DEC-21-2022 JUN TOMMY В4 UPDATE RATED CURRENT MAY-3-2023 JUN TOMMY

Wall thickness=6.4(Max)

1" 3/8-18 UNEF THREAD

38.6



Tightening torque: 4 ~ 6 N·m ✓

NOTES: (UNLESS OTHERWISE SPECIFICATION)

1. MATERIAL:

SHELL: ZINC ALLOY, NICKEL PLATED. INSERT: THERMOPLASTIC, UL94 V-0. NUTS: AL ALLOY NICKEL PLATED. SEAL GASKET: NBR/SILICONE RUBBER. O-RING: NBR/SILICONE RUBBER.

2. SPECIFICATIONS:

2.1 RATED CURRENT: 3A (MAX . 2.2 RATED VOLTAGE: 500V(AC/DC).

2.3 OPERATING TEMPERATURE: SEE CHART.

2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@2000 VOLTS AC.

2.5 INSULATION RESISTANCE: 5000 MEGOHMS MIN.

2.6 IP--CLASS: IP67.

2.7 MATING CYCLES DURABILITY: 500 CYCLES MIN.


2.8 ROHS COMPLIANT.

3. SUITABLE CONTACTS: 16# CONTACTS.

4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

5. CONTACT SIZE AND REAR SEAL WIRE RANGE:

CONTACT SIZE	CONTACT SIZE MIN. INSUL O.D.		WIRE RANGE	
16#	Ø2.0mm	Ø3.2mm	14 - 24AWG	



KEY POS	PART NUMBER					
	-40°C ~ 105°C	-40°C ~ 125°C				
N	RT072028PNH	RT072028PNH03				
W	RT072028PWH	RT072028PWH03				
Х	RT072028PXH	RT072028PXH03				
Y	RT072028PYH	RT072028PYH03				
Z	RT072028PZH	RT072028PZH03				

QUANTITY	PART N	NUMBER		DESCRIPTION				ITEM	
		М	IAT	ERI	ALS	LI	ST		
UNLESS OTHERWISE SPECIFIED  1) All dimensions are in metric(mm).  2) Tolerances are as follows:  1 PL DEC ±0.30   Fractions ±1/84  2 PL DEC ±0.15   Angles ±1°  3 PL DEC ±0.08		SIGNATURES		DATE	Amphenol				
		DRAWN:	JUN	MAY-3-2023	Ampnenor				
		CHECKED:	JOE	MAY-5-2023	Sine Systems - www.amphenol-sine.co				ne.com
3) Note reference =	×	ENGINEER:			44724 Morley Drive Clinton Township, MI 48036				
MATERIAL SPECIFICATIONS:		APPROVAL:	OMMY	MAY-10-2023			17		
		CUSTOMER:		ECO-MATE, RECEPTACLE, JAM NUT, SIZE 20, 28POS, PIN.					
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL							
PROCESS SPECIFICATIONS:				В	C-	RT072028	P*Hx	B4	
NEXT ASSY:				SCALE: NC	DNE		SHEET 1	of 1	

RT072028P\*Hx

ECO-MATE, RECEPTACLE, JAM NUT, SIZE 20, 28POS, PIN

01

9.7