




REV	ECO	
B1	-	














	REVISIONS										
	REV	ECO		DES	SCRIPTION	-	DATE	BY	APPR	1	
	B1	-	RFI		W DWG FORM	AT	05/10/14	DRACK	7.1 1 1.	-	
										-	
	NOTES	: UNLESS	6 OTHER	WISE S	PECIFIED					TITLE:	
1. MATERIAL: INSULATION INSERT: PBT, UL94 V0 SEAL: VITON HOUSING BODY: ZINC DIE CAST, NICKEL PLATED COUPLING NUT: COPPER ALLOY, NICKEL PLATED										M40C, REC., STR, 6POS(4+2), FLANGE MOUNT	
 2. SPECIFICATIONS: 2.1 CURRENT RATING: SIGNAL: 30 AMPS POWER: 75AMPS 2.2 VOLTAGE RATING: SIGNAL: 250V AC/DC POWER: 630V AC/DC 2.3 OPERATING TEMPERATURE: -20°C TO +130°C 2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ SIGNAL: 4000VOLTS AC. 											
POWER: 6000 VOLTS AC. 2.5 DEGREE OF PROTECTION: IP67 (MATED CONDITION) 2.6 DEGREE OF POLLUTION: 3 PER UL840 2.7 OVERVOLTAGE CATEGORY: III PER UL840 2.8 MATING CYCLE DURABILITY: >50 CYCLES									DWG NO: MC1LK		
2.9 RoHS COMPLIANT 3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.									1LKN0601		
										REV: B1 SH: 1	
			₹							٩. Fi	
QUANTITY						SCRIPTI	ION		ITEM]-	
UNLESS OTHERWIS		<u>ר</u>	MAT	ERI		ST				-	
1) All dimensions are in 2) Tolerances are as fol	metric(mm).	DRAWN:	ATURES	DATE 06/23/14	A	m	ohe	no			
1 PL DEC ±0.30 Fi 2 PL DEC ±0.15 Ar	ractions ±1/64	CHECKED:	Tuu	00/23/14		-					
3 PL DEC ±0.08		ENGINEER:			311	44724 Mor	- www.amphenol rley Drive	-Sine.com			
MATERIAL SPECIFICATION		APPROVAL:				Clinton To	wnship, MI 48036	6		4	
MATERIAL OF LOW IDATION		CUSTOMER:									
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY, DESIGN FEATURES, SPECIFICATIONS: SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL								-			
NEXT ASS'Y:		DIMENSIONS A	RE SUBJECT TO NG VARIATIONS	NORMAL		•		IEET 1	 ₀_ 1	1	
							1			<u>م</u>	

MOUNTING HOLE