	D I	Г	Π		0	Ξ	A		
4	Z T T T T T T T T T T T T T T T T T T T	ØS						4	
ယ					LAYOUT SHOWN A	S EXAMPLE		3	
		Keying Shown as ex	ample						
	CHARACTERISTICSStandard : Based on L-DTL-38999 Series III-Shell Material: Aluminium-Shell Plating: Black Zinc Nickel-Insulator: Thermoplastic-Contacts: Copper Alloy-Seals & Grommet: Silicon Elastomer				SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country Jurisdiction & Control List				
N	 -Contact Plating : Gold over copper Alloy 0.8µm minin -Durability : 500 Mating cycles -Delivered without Souriau contacts 		FR Not Listed PN: 8D525Z41PNL						
	-Temperature Range : -65°C to +175°C	A 18-10-2016 First Release							
	-Salt Spray : 500 hours			ISS DATE Designed By:	Latest modification - by Date:	CUS	MOD N°		
			TITLE Aluminium Plug 8D series						
_ _	BASIC SERIES:8D5-25SHELL TYPE : Plug with RFI Shielding	Z 41 P N L	Delivered W/O Contacts	SCALE -	General linea Tolerances:		IPRDS / PROJECT 859	1	
	CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 25 CONTACT TYPE : PIN(500 Matings)			SOURIAU	WWW.SOURIAU	This document is the property of SOURIAU it must not be reproduced or communicated without permission			
	PLATING : Z = Black Zinc Nickel		CONTACT LAYOUT : 25-41	format A3		U DRG N° 241PNL-C	SHEET 1/2		
L	H G	F	E	D	C	В	Α		

ſ	т	۵	П	п	D	C	σ	A		1
4		Contact Layout 41 22#22D, 3#20 11#16, 2#12 3#8 Triax								4
	Ctc X A 0 B 7.09 C 10.77 D 12.94 E 13.27 F 8.17 G 4.67 H 0 J -4.67	Y Ctc X Y 10.79 Y -5.37 7.92 11.34 Z 3.32 5.72 7.92 a 7.96 -0.42 3.39 b 0 -6.6 -1.62 c -7.96 -0.42 -6.44 d -3.32 5.72 -12.53 e 0 4.48 -13.37 f 3.02 3.07 -12.53 g 5.32 0.005							-	
ى ت	K -8.17 L -13.27 M -12.94 N -10.77 P -7.09 R 5.37 S 7.32 T 10.39 U 1.77 V -1.77 W -10.39 X -7.32	-6.44 h 3.7 -2.43 -1.62 i 2.38 -4.74 3.39 j -2.38 -4.74 7.92 k -3.7 -2.43 11.34 m -5.32 0.005 7.92 n -3.02 3.07 3.91 p 0 1.81 0.67 q 2.59 -0.01 -9.66 r 0 -3.53 -9.66 s -2.59 -0.01 0.67 t 0 -0.86 3.91 0 -0.86								3
	_					due to a use of the Pro the Specifications issued by	ole for any non-conformity or d oducts which does not comply o r either of the Parties or by a th mmendation, technical notice.)	with nird party		
N						PN: 8D		& Control List Listed		2
					A 18-10-2016 ISS DATE Designed By: TITLE	5 First Release Latest modification - by Date:	cus Aluminium Plug 8D se	STOMER DRAWING	MOD N°	
4					SCALE NA SOURIAU	Genera Toler.	al linear N ances: 	IPRDS / PROJECT 859 This document is the proper SOURIAU it must not be reproduced	or	1
	Н	G	F	E	FORMAT A3 D		RIAU DRG N° 25Z41PNL-C B	communicated without perm		