
т	۵	н т	m	O







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 13

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Composite	
-Shell Plating	: Olive drab Cadmium	
-Insulator	: Thermoplastic	
-Contacts	: Copper Alloy	
-Seals & Grommet	: Silicon Elastomer	
-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum	
-Durability	: 500 Mating cycles	
-Delivered with Souriau contacts and Accessories		
-Temperature Range	-65℃ to +175℃	
-Salt Spray	: 2000 hours	

: 19.6 g ± 10%

8D 0

G

13

J

35

В

F

Ν

Connector dimension				
Dim	Nominal			
Р	3.25±0.2			
PP	4.93±0.2			
R1	23.01			
R2	20.62			
S	28.6±0.3			
V'	19.5+1.4/-0			
W'	2.1/3.65			
Ζ'	32 Max			
VV THREAD	M18x1-6g			


ORIENTATION : N

CONTACT LAYOUT : 13-35

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for a due to a use of the Products w the Specifications issued by either (professional recommend



	σ		A				
S EX4	AMPLE				3		
s whic er of t	non-conformit ch does not co he Parties or b n, technical n	mply with by a third part	у				
untry FR	Jurisdiction & Control List Not Listed						
.3J3	J35BN						
				MOD N°			
		CUSTOMER	RDRAWING				
site	e Receptacle 8D series						
ar			PROJECT 59		1		
J.CC	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
U DRG N° J35BN-C				SHEET			
0122	BBIN-C		Α	÷/	J		

