

т	۵	н т	m	0







LAYOUT SHOWN AS

Keying Shown as example

F

F

CHARACTERISTICS

SHELL SIZE : 17

PLATING : M = Nickel

Н

ω

-Standard : Based on MIL-DTL-38999 Series III

~	Standard : Based on h								
		: Composite						Р	I
		-						РР	∔
	-Shell Plating	: Nickel						R1	∔
	-Insulator	: Thermoplastic						R2	╀
	-Contacts	: Copper Alloy						S V'	╀
	-Seals & Grommet	: Silicon Elastomer						W'	t
\sim	-Contact Plating	: Gold over copper Alloy 0.	8µm mi	nimum				Z'	I
	-Durability	: 500 Mating cycles						VV THREAD	
	-Delivered with Souria	u contacts and Accessories							
	-Temperature Range	 -65°C to +200°C 							
	-Salt Spray	: 2000 hours							
	-Mass	: 22.8 g ± 10%							
	-101035	. 22.0 g ± 10/0							
	BASIC SERIES:	8D 0	-	17 M	26	А	в	I	
		0000		17 101	20				
-	SHELL TYPE : Square	-lange Receptacle							
	CONTACT TYPE : Sta	ndard Crimp Contact							
							L		-

G


Dim	Nominal	
Р	3.25±0.2	
РР	4.93±0.2	
R1	26.97	
R2	24.61	
S	33.3±0.3	
V'	19.5+1.4/-0	
W'	2.1/3.65	
Ζ'	32 Max	
VV THREAD	M25x1-6g	


ORIENTATION : B

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 17-26





Β		A					
R				4			
AS EXAMPLE				3			
any non-conformity or damage swhich does not comply with er of the Parties or by a third party adation, technical notice.)							
	CUSTOMER	DRAWING	MOD N°				
ite Receptacle 8D series							
ar :	NPRDS / PROJECT 859						
J.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission							
U DRG N° M26AB-C			SHEET				
B		A	-, -	J			

