
ר בר		D	0	Ξ		
Z'	ØS					
			LAYOUT SHOW	N AS EXAMPLE		
	Keying Shown as example					
CHARACTERISTICS	Connector dimension	1				
Standard : Based on MIL-DTL-38999 Series III	DimNominalØS32.5 Max					
-Shell Material: Composite-Shell Plating: Nickel-Insulator: Thermoplastic-Contacts: Copper Alloy	Z' 31.5 Max VV THREAD M22x1-6g		SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum			F		& Control List	
-Durability : 500 Mating cycles						
-Delivered without Souriau contacts			PN: 8D515M15PAL			
-Temperature Range : -65°C to +200°C		A 19-10-2	2016 First Release			
-Salt Spray : 2000 hours -Mass : 19.9 g ± 10%		ISS DAT	E Latest modification - by		MOD) N°
		Designed By:	Date:	CUS	TOMER DRAWING	
		TITLE	Composite Plug 8D series			
BASIC SERIES: 8D 5 - 15 M SHELL TYPE : Plug with RFI Shielding	15 P A L Delivered W	O Contacts NA	General Toleran ±	ices:	PRDS / PROJECT 859	
CONTACT TYPE : Standard Crimp Contact			WWW.SOURI		This document is the property of SOURIAU it must not be reproduced or	
SHELL SIZE : 15	CONTACT TYPE : PIN(50				ommunicated without permission	
		OUT - 15-15 FORMAT				ET
PLATING : M = Nickel	CONTACT LAY	A3	SOUR	NAU DRG N°	SHEE	

_	т	G	ال	m		0	
		Contact Layout $x \xrightarrow{k} \xrightarrow{k} \xrightarrow{k} \xrightarrow{k} \xrightarrow{k} \xrightarrow{k} \xrightarrow{k} \xrightarrow{k}$					
4		H G G F F F F F F F F F F F F F F F F F					
	A +100 (2:54) B +202 (2:513) C +244 (6:20) D +218 (5:54) E +126 (3:20) F +000 (0:0) G -126 (3:20) H -218 (5:54) Shell Arrangement no. Nun	+225 (5.72) J -244 (6.20) +014 (0.36) +140 (3.56) K -202 (5.13) +140 (3.66) +014 (0.36) L -100 (2.54) +225 (5.72) -113 (2.87) M +000 (0.0) +140 (3.56) -209 (5.31) N +110 (2.79) +040 (1.02) -246 (6.72) P +000 (0.0) -77 (1.96) -209 (5.31) R -110 (2.79) +040 (1.02) -113 (2.87) mber of size contacts Service Contact rating location Supresedes					
ω		1 16 I P MS20052-15 14 20 I All other MS20052-15					
	-					SOURIAU shall not be liab due to a use of the Pro the Specifications issued by	oducts w v either c
N						(professional recor PN: 8DS	Count FR
					A 19-10-20 ISS DATE Designed By:	16 First Release	
<u> </u>					TITLE SCALE NA	Genera Tolera	Compo al linear ances:
					FORMAT	U WWW.SOUR SOU	
		<u> </u>	F	F T	A3	8D5	15M
	Н	l G	F	E	D	C	



 \triangleright

σ