
	I	۵	П	m			0	U D	A		
4		V Thread	ØS								4
ω							LAYOUTS	HOWN AS EXAMPLE			3
			Keying Shown as	s example							
	CHARACTERISTICS	ries III	F	Connector dimension Dim Nominal	7						
		ØS38.5 MaxZ'31.5 Maxell Plating: Olive drab Cadmiumsulator: Thermoplastic				SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)					
N	-Seals & Grommet : Silicon Elaston -Contact Plating : Gold over cop	ner per Alloy 0.8µm minimum						Country Jurisd	iction & Control List Not Listed		2
	-Durability : 500 Mating cy -Delivered without Souriau contacts					PN: 8D519J32SBL					
	-Temperature Range <sub>:</sub> -65°C to +175 -Salt Spray : 2000 hours	°C				A 18-10-2010	6 First Release				-
	-Mass : 31.9 g ± 10%					ISS DATE Designed By:	Latest modification - by Date:		CUSTOMER DRAWING	MOD N°	
						TITLE	Composite Plug 8D series			-	
<b>_</b>	BASIC SERIES: 8 SHELL TYPE : Plug with RFI Shielding	D 5 - 19 J	32 S B		N/O Contacts	SCALE NA		neral linear blerances: ±	NPRDS / PROJECT <b>859</b>		-
	CONTACT TYPE : Standard Crimp Contact					SOURIAU WWW.SOURIAU.COM		SOURIAU it must not be reprodu	it must not be reproduced or		
	SHELL SIZE : 19 PLATING : J = Olive drab Cadmi	um			YOUT : 19-32	FORMAT		URIAU DRG N°	communicated without pe	ermission SHEET	-
		<u></u>		E T	-	A3		D519J32SBL-C	Δ	1/2	
	H	G	Г		$\bigvee$	D	С	l B	I A		

CONTACT TYPE	: Standard Crimp Contact

T G	m m		C	Ξ	A	
	ØS		Image: constraint of the sector of the sec	WN AS EXAMPLE		4
HARACTERISTICS tandard : Based on MIL-DTL-38999 Series III	Keying Shown as example Connector dimension Dim Nominal	]				
Chell Material: CompositeChell Plating: Olive drab CadmiumInsulator: ThermoplasticContacts: Copper Alloy	ØS         38.5 Max           Z'         31.5 Max           VV THREAD         M28x1-6g		the Specifications issued by	ducts which does not com	nply with v a third party	
eals & Grommet: Silicon ElastomerContact Plating: Gold over copper Alloy 0.8μm minimumDurability: 500 Mating cyclesDelivered without Souriau contacts			PN: 8D		tion & Control List Not Listed	2
Temperature Range: -65°C to +175°CSalt Spray: 2000 hoursMass: 31.9 g ± 10%		A 18-10-201 ISS DATE Designed By:	16 First Release Latest modification - by Date:		CUSTOMER DRAWING	D N°
		TITLE		Composite Plug 8D		
ASIC SERIES: 8D 5 - 19 J HELL TYPE : Plug with RFI Shielding ONTACT TYPE : Standard Crimp Contact HELL SIZE : 19	32 S B L Delivered W ORIEL CONTACT TYPE : SOCKET(50	NTATION : B SOURIAL		al linear ances:  IAU.COM	NPRDS / PROJECT <b>859</b> This document is the property of SOURIAU it must not be reproduced or communicated without permission	1
LATING : J = Olive drab Cadmium	CONTACT LAY		8D5	RIAU DRG N° 519J32SBL-C	SHI	
H G I	F I E	D	С	В	A	



	1	σ	1	А			
						ן	
						4	
						3	
all not be liable for any non-conformity or damage use of the Products which does not comply with ons issued by either of the Parties or by a third party essional recommendation, technical notice.)							
	Country	Jurisd	liction & Contr	ol List		0	
	FR		Not Listed			2	
PN: 8	D519J3	2SBL					
ation - by					MOD N°		
te:			CUSTOMER	DRAWING			
Composite Plug 8D series							
Gene	ral linear		NPRDS / I	PROJECT			
Tole	erances: ±		85	9		4	
	-		This docu	ment is the prop	perty of	1	
W.SOURIAU.COM it must not be reproduced or communicated without permission							
SOURIAU DRG N° SHEET							
	8D519J32SBL-C 2/2						
		В		А		,	