ſ	Ŧ	Q		П		m			0
4 ω			 VV Thread 		S	ØA			
				Keying Sho	wn as example				
N	-Contact Plating : Gold o	ss Steel ated oplastic r Alloy Elastomer ver copper Alloy 0.8μm	minimum			r dimension Nominal 49.2±0.3 33.32+0.1/-0.15 32.5Max 46±0.4 3+0.9/-0.1 M28x1-6g			SOURIAU sha due to a us the Specificatio (profes
	-Delivered with Souriau contacts	to +200°C						A 30-09-2016 ISS DATE Designed By: TITLE	First Release Latest modifica Date
-	BASIC SERIES: SHELL TYPE : Jam nut Receptac CONTACT TYPE : Standard Crin SHELL SIZE : 19		19 K	35 A N		NTACT TYPE : PIN(5	00 Matings)	SCALE NA SOURIAU	wwv
	PLATING : K = Passivated	1				CONTACT LAY	OUT : 19-35	format A3	
L	Н	G		F		E	7 D		С

 \forall

	ω		А				
					4		
LAYOUT SHOWN AS EXAMP	LE				3		
all not be liable for any non-conformity or damage use of the Products which does not comply with ons issued by either of the Parties or by a third party essional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed PN: 8D719K35AN							
ation - by MOD N° te: CUSTOMER DRAWING							
Stainless Steel Receptacle 8D series General linear Tolerances: t 859							
W.SOURIAU.COM it must not be reproduced or communicated without permission							
SOURIAU DRG N° SHEI 8D719K35AN-C 1/2							
BA							

ſ	Т	۵	н т	п	D	C	σ	A	_
4	-X (1 3	Contact Layout				Panel cutout JAM NUT RECEPTACLE (TYPE 7)			4
	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) 0.00 (2.29) 34 +.045 (1.14) +.360 (9.14) 0.00 (0.00) 35 +.045 (1.14) +.360 (9.14) 0.00 (2.29) 36 +.045 (1.14) +.270 (6.86) 0.90 (2.29) 36 +.045 (1.14) +.180 (4.57) 2.25 (5.72) 37 +.045 (1.14) +.090 (2.29) 0.45 (1.14) 39 +.045 (1.14) +.090 (2.29) 0.45 (1.14) 39 +.045 (1.14) 090 (2.29) 0.45 (1.14) 40 +.045 (1.14) 180 (4.57) 1.35 (3.43) 41 +.045 (1.14) 270 (6.86) 2.25 (5.72) 42 +.045 (1.14) 360 (9.14) +.270 (6.86) 43 +.123 (3.12) +.315 (3.43) 000 (0.00) 46 +.123 (3.12) +.315 (3.43) 000 (0.02) 45 +.123 (3.12) +.135 (3.43) 000 (0.00) 46 +.123 (3.12) 045 (1.14) 000 (0.00) 46 +.123 (3.12) 04				Dim Nominal B 33.91+0/-0	.25		
	Contact position ID Loca 18 123 (3.12) 19 123 (3.12) 20 123 (3.12) 21 123 (3.12) 22 123 (3.12) 23 .123 (3.12) 24 123 (3.12) 25 045 (1.14) 26 045 (1.14) 27 045 (1.14) 28 045 (1.14) 29 045 (1.14) 29 045 (1.14)	Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) +225 (5.72) 51 +201 (5.11) +270 (6.80) +135 (343) 52 +201 (5.11) +1090 (2.29) -045 (1.14) 53 +201 (5.11) +000 (2.29) -135 (3.43) 55 +201 (5.11) +000 (2.29) -225 (5.72) 56 +201 (5.11) -000 (2.29) -236 (8.00) 67 +201 (5.11) -000 (2.29) -246 (1.14) 58 +279 (7.09) +125 (3.43) +360 (9.14) 58 +279 (7.09) +215 (3.43) +380 (4.57) 60 +279 (7.09) +045 (1.14) +000 (2.29) 61 +279 (7.09) -045 (1.14) +000 (0.00) 62 +279 (7.09) -045 (3.43) +000 (0.00) 62 +279 (7.09) -045 (3.43) -000 (0.29) 63 +279 (7.09) -035 (3.43)					ole for any non-conformity or da oducts which does not comply v	_	3
2	31 045 (1.14) 32 045 (1.14) 33 045 (1.14) Shell Arrangement No.	180 (4.57) 64 +.357 (9.07) +.090 (2.29) 270 (6.86) 65 +.357 (9.07) +.000 (0.00) 360 (9.14) 66 +.357 (9.07) 090 (2.29) (Applicable to MIL-DTL-38999 only) umber of ontacts Service Contact Superse ontacts Superse fraging 66 22D M All MS27530	tes			the Specifications issued by (professional recor PN: 8 E	veither of the Parties or by a the mmendation, technical notice.)	ird party	2
					A 30-09-20 ISS DATE Designed By:	016 First Release Latest modification - by Date:	CUS	MOD N°	,
		TITLE Stainless Steel Receptacle 8D series							
<u> </u>					SCALE NA		ances: ±	PRDS / PROJECT 859 This document is the property of	_ 1
					SOURIA		RIAU.COM	SOURIAU it must not be reproduced or ommunicated without permission	
		1 -	_		FORMAT A3	8D7	RIAU DRG N° 719K35AN-C	SHEET 2/2	
	Н	G	I F	I E	D	C	В	A	