RL0603A Series

Features


- EIA size:0603
- Variable capacitance
- Operating voltage: 3.3Vdc ~33Vdc
- High surge suppress capability
- Bidirectional and symmetrical V/I characteristics
- Multilayer ceramic construction technology
- RoHS & Halogen Free (HF) compliant
- Operating temperature range: -55°C ~ +125°C
- Storage temperature range: 5°C ~ +40°C



Applications

- ı Used to Help Achieve Electromagnetic Compliance of End Products
- Provides On-Board Transient Voltage Protection for ICs, CMOS and MOSFET
- Suppression of Inductive Switching or Other Transient Events Such as EFT and Surge Voltage at the Circuit Board.
- Protection of Components and Circuits Sensitive to ESD Transients Occurring on Power supplies, Control and Signal Lines.

Part Number Code



Revised: 2021-7-09







RL0603A Series

Electrical Characteristics

Type Number	Varistor Voltage		lowable tage	Max. Energy (10/1000μs)	Vol	amping tage 0µs)	Withstanding Surge Current (8/20µs)
	V _{1mA} (V)	V _{AC} (V)	V _{DC} (V)	(J)	I _P (A)	V _c (V)	I(A)
RL0603A5R0K	4~6	2	3.3	0.1	1	13.2	20
RL0603A8R0K	6.7~10.1	4	5.6	0.1	1	22.2	20
RL0603A120K	10.8~16.2	6	9	0.1	1	35.6	20
RL0603A180K	16.8~21	11	14	0.1	1	46	30
RL0603A210K	19.2~24	12	16	0.1	1	52	30
RL0603A240K	21.6~27	14	18	0.1	1	59	30
RL0603A270K	26.4~33	17	22	0.1	1	72	30
RL0603A300K	28.8~36	18	24	0.1	1	79	30
RL0603A330K	31.2~39	20	26	0.1	1	85	30
RL0603A360K	33.6~42	21	28	0.3	1	78	30
RL0603A390K	36~45	25	30	0.3	1	99	30
RL0603A420K	39.6~49.5	28	33	0.3	1	108	30

Environmental Performance

Item	Specifications	Test Condition
Bias Humidity	V _V / V _V ≤±10%	90%RH, 40°C, Working Voltage, 1000 hrs
Thermal Shock	V _V / V _V ≤±10%	-40°C to85°C,30min.cycle,5 cycles
Full Load Voltage	V _V / V _V ≤±10%	Working Voltage,85°C,1000 hrs

General Technical Data


Response Time	<1ns		
Solderability	245±5 °C, 3±1sec		
Solder leach resistance		260±5 °C,10±1sec	
	Storage Temperature	5~40°C	
Taping Package Storage Condition	Relative Humidity	To 65%	
	Storage Time	12 Months max	





RL0603A Series

Soldering Parameters - Reflow Soldering (Surface Mount Devices)



Precaution for soldering	Precai	ution	for	so	Iderine	a
--------------------------	--------	-------	-----	----	---------	---

Note that this product will be easily damaged by rapid heating, rapid cooling or local heating.

Do not give heat shock over 100°C in the process of soldering. We recommend to take preheating and gradual cooling

Soldering gun procedure

Note the follows, in case of using solder gun for replacement.

- 1)The tip temperature must be less than 280 for the period within 3 seconds by using soldering gun under 30W
- 2) The soldering gun tip shall not touch this product directly.


Soldering volume

Note that excess of soldering volume will easily get crack the body of this product.


Reflow Condition		Pb - Free assembly	
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	- Time (min to max) (t _s)	60 -180 Seconds	
Average ramp up rate (Liquids Temp T _L) to peak		3°C/second max	
T _{S(max)} to TL - Ramp-up Rate		3°C/second max	
Reflo	- Temperature (T _L) (Liquids)	217°C	
W	- Time (min to max) (t _s)	60 -150 Seconds	
Peak Temperature (T _P)		260 +0/-5°C	
Time within 5°C of actual peak Temperature (t _p)		20 - 40 Seconds	
Ramp-down Rate		6°C/second max	
Time 25°C to peak Temperature (T _P)		8 minutes Max	
Do not exceed		260°C	

Dimensions





Revised: 2021-7-09



Recommended Soldering Pad Layout

Symbol	Millimeters	Inches
L	1.52±0.25	0.06±0.01
w	0.76±0.25	0.03±0.01
T _{max} .	1.01	0.04
WB	0.30±0.15	0.012±0.006
ı	0.9	0.035
J	2.54	1
K	0.51	0.02









RL0603A Series

Taping and Reel Specifications



Symbol	Millimeters	Inches
w	8.00±0.20	0.315±0.008
E	1.75±0.10	0.069±0.004
F	3.50±0.05	0.138±0.002
D	1.55±0.05	0.061±0.002
P	4.00±0.10	0.157±0.004
P0	4.00±0.10	0.157±0.004
P2	2.00±0.05	0.079±0.002
LO	1.88±0.10	0.074±0.004
WO	1.08±0.10	0.043±0.004

Packing Specifications



Symbol	Millimeters	Inches
D0	13.0±0.2	0.512±0.008
D1	178±2.0	7.008±0.079
D2	Ф60.0±0.5	Ф2.362±0.02
W1	9.3±0.5	0.366±0.02

Taping Specifications

There Shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the heat of taping.

Quantity of products in the taping package

SIZE EIA (EIAJ)	0603
Standard Packing Quantity(PCS/reel)	4000

