



| | | | | | | | | | | | | |
|---|-----------------------------------|---|-----------------|------------------------------|-----------------------------|--------------------------|-------------------|--------------------------|-----------------|-----------------|-----------------|--|
| Number of contacts | Standard | 3 | 4 | 5 | 5 | 6 | 7 | 7 | 8 | 12 | 14 | |
| Contact arrangement | DIN EN 61076-2-106 | 03-a | 04-a | 05-a | 05-b | 06-a | 07-a | 07-b | 08-a | 12-a | 14-a | |
| Contact arrangement | IEC 60130-9 ¹⁾ | yes | no | yes | no | yes | no | yes | no | | | |
| Rated voltage ²⁾ | IEC 60664-1 | 300 V (100 V) | 300 V (63 V) | 100 V (32 V) | 300 V (63 V) | 100 V (32 V) | 150 V (32 V) | 150 V (32 V) | 150 V (32 V) | 150 V (32 V) | 150 V (32 V) | |
| Rated voltage | UL 1977 | 250 V | | | | | | | | 60 V | | |
| Rated impulse withstand voltage ²⁾ | IEC 60664-1 | 1500 V (1500 V) | | 1200 V (800 V) | 1500 V (1500 V) | | 1200 V (800 V) | | | | | |
| Pollution degree ²⁾ | IEC 60664-1 | 1 (2) | | | | | | | | | | |
| Installation category | IEC 60664-1 | I | | | | | | | | | | |
| Insulation group | IEC 60664-1 | II, 400 ≤ CTI < 600 | | | | | | | | | | |
| Current rating | IEC 60512-5-2 UL 1977 | 10A/+40°C | | 7A/+40°C | | | | | 3A/+40°C | | | |
| Insulation resistance | IEC 60512-3-1 | >10 ¹⁰ Ohm ³⁾ | | | | | | | | | | |
| Contact resistance | IEC 60512-2-1 | <5m Ohm | | | | | | | | | | |
| Climatic category | IEC 60668-1 | 40 / 100 / 56 | | | | | | | | | | |
| Temperatur range | IEC 60668-1 | -40°C...+100°C / -40°F...+212°F | | | | | | | | | | |
| IP degree | IEC 60529 | IP 40 | | | | | | | | | | |
| Insertion and withdrawal force | IEC 60512-13-2 | 25N | 30N | 35N | 35N | 50N | 55N | 5N | 60N | 50N | 50N | |
| Mechanical operation | IEC 60512-9-1 | silver ≥500 mating cycles gold ≥1000 mating cycles | | | | | | | | | | |
| Housing material | | brass or zinc die cast nickel plated or thermoplast | | | | | | | | | | |
| Dielectric material | | thermoplastic | | | | | | | | | | |
| Contacts | | silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0157 X U (12-14pol) | | | | | | | | | | |
| Termination technique | | crimp | | | | | | | | | | |
| Wire gauge | | 0,09-1,0mm ² | | 0,09-0,75 mm ² | 0,09-1,0 mm ² | 0,09-0,75mm ² | | 0,09-0,25mm ² | | | | |
| Flamability | | UL 94 VO | | | | | | | | | | |
| locking system | IEC 60130-9 DIN EN 61076-2-106 | metal screw coupling; tightening torque 0,7-1,5 Nm | | | | | | | | | | |

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
 All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffungsgarantie" or "Haltbarkeitsgarantie").

| | | |
|--|---|--------------|
| | 14 (14-a) | T 3651 551 U |
| | 12 (12-a) | T 3636 551 U |
| | 8 (08-a) | T 3505 551 U |
| | 7 (07-b) | T 3485 551 U |
| | 7 (07-a) | T 3476 551 U |
| | 6 (06-a) | T 3401 551 U |
| | 5 (05-b) | T 3357 551 U |
| | 5 (05-a) | T 3361 551 U |
| | 4 (04-a) | T 3301 551 U |
| | 3 (03-a) | T 3261 551 U |
| | 2 (Pin 1+3) | T 3201 551 U |
| Contact arrangement View on mating side | Number of contacts (Contact arrangement acc. DIN EN 61076-2-106) | Part number |

| | | | | | | | |
|---|--|------------------------|--|------------------------------------|--|--|--|
| Gewicht (errechnet) / Calc WT: 29,036 g | | Zul. Abw./Tolerances: | | Maßstab / Scale: 2:1 | | A3 | |
| Prüfmaß / Testdimension | | ISO 2768-c | | DIN / ISO 13715 | | CUSTOMER DRAWING | |
| Teileindex / Partindexnumber: | | Bagatelle change: | | Gez. Drawn: 15.06.2021 MCARLE | | Status Released | |
| 02 202100006 | | 15.06.2021 MCARLE | | Gepr. Checked: 16.06.2021 MBERTSCH | | Female cable connector female cable connector | |
| Index | | Änderung / Description | | Datum / Date | | Name | |
| 02 | | 202100006 | | 15.06.2021 | | MCARLE | |
| | | | | | | Amphenol Tuchel Industrial GmbH | |
| | | | | | | M DA T 3XXX 551 U | |
| | | | | | | Ers. f. l. Replacement for: M-DA T 3XXX 551 U Rev.01 | |

Coping of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

FAI2021-002722
 NXM-V02
 Blatt / Sheet 1
 1 Bl.