

HDP24-24-91PN-P064 ✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HDP

TE Internal #: HDP24-24-91PN-P064

Housing for Male Terminals, Wire-to-Wire, 9 Position, Sealable, Black, Wire & Cable, Power & Signal, Panel Mount, -67 – 257 °F [-55 – 125 °C], Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Connector System: **Wire-to-Wire**

Number of Positions: **9**

Connector & Housing Type: **Housing for Male Terminals**

Sealable: **Yes**

Mating Pin Diameter: **1.59 mm, 2.39 mm, 3.61 mm [.063 in, .094 in, .142 in]**

[All DEUTSCH HDP20 Housings \(324\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Contact Retainer

Configuration Features

Blank Cavity Position	0
Connector Seal Code	N Seal
Number of Positions	9

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 12, Size 16, Size 8
Contact Type	Pin
Mating Pin Diameter	1.59 mm, 2.39 mm, 3.61 mm [.063 in][.094 in] [.142 in]
Contact Current Rating (Max)	13 A, 25 A, 60 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Add By Accessory
Mating Alignment Type	Guide Post
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA GF
------------------	-------

Dimensions

Connector Height	47.63 mm[1.875 in]
Product Width	50.8 mm[2 in]
Product Length	41.86 mm[1.648 in]
Compatible Insulation Diameter Range	2.54 – 3.4 mm, 3.4 – 4.32 mm, 4.83 – 6.1 mm [.1 – .134 in][.134 – .17 in][.19 – .24 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
-------------	-----



Connector Position Assurance Capable

No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-J67-DSCC16
DEUTSCH Size 16 Crimp Contacts




TE Part # 24-D-PUNCH
D-HOLE PUNCH, SIZE 24



TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK



TE Part # 16-04477
GASKET, 24SZ, BLK, HD30



TE Part # 1060-12-0144
PIN, SF, SIZE 12, 12-14, AU/SN



TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY



TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK



TE Part # 114008-ZZ
EXT TOOL, SIZE 8, 8-10 AWG, N, GRN



TE Part # 0411-291-1405
EXT TOOL, SIZE 16, 14-16 AWG, N, GRN



TE Part # WHDS-24-1
STRAIN RELIEF, HD30, 24SZ, ST



TE Part # 114010-ZZ
EXT TOOL, SIZE 12, 12 AWG, N, YEL



TE Part # WHDS-24-2
STRAIN RELIEF, HD30, 24SZ, RA



TE Part # 0411-204-1605
EXT TOOL, SIZE 16, 16-18 AWG, N, DRK BLU



TE Part # 1060-12-0222
PIN, SF, SIZE 12, 10, NI/NI




TE Part # 1060-12-0166
PIN, SF, SIZE 12, 12-14, NI/SN




TE Part # 2300908-1
0460-003-16329, PIN, SOLID, 20-24AWG, AU


Also in the Series | **DEUTSCH HD**




Automotive Connector Caps & Covers
(32)



Automotive Housings(742)



Connector Backshells(29)



Connector Seals & Cavity Plugs(10)




Connector Strain Relief(5)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(11)



PCB Headers & Receptacles(1)

Also in the Series | **DEUTSCH HDP**



Automotive Connector Caps & Covers (4)



Automotive Housings(331)



Connector Backshells(8)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(5)

Customers Also Bought



TE Part #DT04-12PA-BL10
REC, 12P, BLK, E, ENH KEY, XCAP, FLANGE,A



TE Part #HDP26-24-91SN-P064
DEUTSCH HDP20 Housings



TE Part #0460-204-08141
PIN, SOLID, SIZE 8, 8-10AWG, NI



TE Part #3-794681-2
02P MICRO MNL ASSY,VRT,THRU,LF



TE Part #2063524-1
SDE MCP1.5 0.2-1.0mm2 ASSY



TE Part #K1070514
Schlagschalter (Hauptantr HK) 06-63-420



TE Part #2819656-1
DT06-3S-EP06



TE Part #6-1355512-7
47 WAY ABS CONNECTOR



Documents

Product Drawings

[REC, 9P, BLK, N, NO JMP, 8/12/16, P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_HDP24-24-91PN-P064_C1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HDP24-24-91PN-P064_C1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HDP24-24-91PN-P064_C1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English