

# F-25X

## Electrical Specifications (@25C)

1. Maximum Power: 18.9 VA
2. Primary: 115V 50/60 Hz
3. Secondary: 12.6VCT @ 1.5 Amps
4. Voltage Regulation: 15 % TYP @ full load to no load
5. Temperature Rise: 35C TYP (45C MAX allowed)

## Description:

The F-25X is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

## Construction:

Wound on a single channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

## Safety:

These products are 100% hipot tested with an insulation of 1500V between primary and secondary windings as well as between the primary / secondary windings and the core.


## Dimensions: Units: In inches

| A     | B     | C    | D     |
|-------|-------|------|-------|
| 1.937 | 3.312 | 2.00 | 2.812 |

Mounting Hole Diameter: 0.187 in

Weight: 1.30 lbs

## Schematic:



## Connections:

Transformer is provided with 7" (178mm) long, 0.25" (6mm) stripped and tinned, stranded 22 AWG, UL1015 lead wire.

**Primary:** Black to Black

**Secondary:** Blue to Blue

**RoHS Compliance:** As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

\* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

