

7-1123722-2 ✓ ACTIVE



Economy Power

TE Internal #: 7-1123722-2

Rectangular Power Connectors, Housing, Plug, Wire-to-Board, 2 Position, 3.96 mm [.156 in] Centerline, Wire & Cable, UL 94V-2, Economy Power

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Insulation Resistance	1000 MΩ
Operating Voltage	250 VDC

Contact Features

Contact Layout	Inline
Contact Current Rating (Max)	8 A



Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Retention	With
Mating Alignment	Without
Mating Retention Type	Latch, Locking Latch
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	3.96 mm [.156 in]
Housing Color	Natural
Housing Material	Nylon 66

Dimensions

Connector Height	10.5 mm [.413 in]
Product Width	13.3 mm [.524 in]
Product Length	7.86 mm [.309 in]
Compatible Insulation Diameter Range	1.7 – 3 mm [.067 – .118 in]

Usage Conditions

Operating Temperature Range	-25 – 105 °C [-13 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	4000
Packaging Method	Bag

Product Compliance









[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1744036-2 02P ECONOMY POWER .200 CL HSG</p>	 <p>TE Part # 2132813-2 2 pos. EP II housing w/rtnr</p>	 <p>TE Part # 1-1123722-5 3.96 EP PLUG HSG 5P(NATURAL)</p>	 <p>TE Part # 1744416-2 2 POS EP II HSG, GLOW WIRE</p>
 <p>TE Part # 1-1123722-6 3.96 EP PLUG HSG 6P(NATURAL)</p>	 <p>TE Part # 1-1123722-2 3.96 EP PLUG HSG 2P(NATURAL)</p>	 <p>TE Part # 1-1123722-3 3.96 EP PLUG HSG 3P(NATURAL)</p>	 <p>TE Part # 3-1123722-2 3.96 EP PLUG HSG 2P(BLUE)</p>



TE Part # 7-1123722-5
3.96 EP PLUG HSG 5P(NATURAL)



TE Part # 2108743-1
POWER 2P DBL L/PRO NAT




TE Part # 7-1123722-1
3.96 EP PLUG HSG 11P(GWT750)



TE Part # 7-1123722-4
3.96 EP PLUG HSG 4P(NATURAL)


Also in the Series | Economy Power



Connector Contacts(15)




Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(162)



Rectangular Connector Housings(1)



Rectangular Power Connectors(301)



Wire-to-Board Connector Assemblies & Housings(142)

Customers Also Bought



TE Part #4030-002-120
2G TRIAXIAL MEMS DC ACCELEROMETER



TE Part #104257-7
08 MTE RCPT HSG SR LATCH .100



TE Part #5-103735-6
07 MTE HDR SRST LATCH .100CL



TE Part #5-103735-2
03 MTE HDR SRST LATCH .100CL



TE Part #1318912-1
EP CONN LP REC





TE Part #104257-2
03 MTE RCPT HSG SR LATCH .100



TE Part #5-103735-1
02 MTE HDR SRST LATCH .100CL



TE Part #1-1123723-2
3.96 EP HDR ASSY 2P(NATURAL)



Documents

Product Drawings

3.96 EP PLUG HSG 2P(NATURAL)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_7-1123722-2_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1123722-2_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1123722-2_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English