

Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		
APPLICATION STANDARD											
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C			STORAGE TEMPERATURE RANGE	--- °C TO --- °C					
	VOLTAGE	200V AC			OPERATING HUMIDITY RANGE	--- % TO --- %					
	CURRENT	2 A			APPLICABLE CABLE	AWG#26~36					
SPECIFICATIONS											
ITEM		TEST METHOD			REQUIREMENT			QT	AT		
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT. ACCORDING TO DRAWING					X	X			
MARKING		CONFIRMED VISUALLY					X	X			
ELECTRICAL CHARACTERISTICS											
INSULATION RESISTANCE		500 V DC			1000 MΩ MIN.			X	-		
VOLTAGE PROOF		650 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN			X	-		
ENVIRONMENTAL CHARACTERISTICS											
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C. 90~95 %, 96 h.			1)INSULATION RESISTANCE: 1000 MΩ MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-		
RAPID CHAGE OF TEMPERTURE		TEMPERTURE-55→15~35→ 85→15~35°C TIME 30→10~15→ 30 → 10~15 min. UNDER 5 CYCLES.			NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-		
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED			
				M.ISHIZUKA 99.09.25	H. Okawa 99.09.25	<i>M. Yamaguchi</i> 99.09.25	<i>M. Yamaguchi</i> 99.09.25				
UNLESS OTHERWISE SPECIFIED, REFER TO MIL-STD-1344											
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST											
HRS HIROSE ELECTRIC CO.,LTD.				SPECIFICATION SHEET			PART NO.			A3B - 24D - 2C	
				CODE NO.(OLD)	DRAWING NO.			CODE NO.			1
CL		ELC4 - 021400			CL 621 - 0313 - 6						

TO
PCK